



Metric table

Dimensions in: millimeters - inches

Length l_1	d_1 Blind bore	d_2	d_3	d_4	h_1	h_2	h_3	h_4	h_5 min.	h_6	h_7	h_8	l_2	t	\varnothing Handle
80 3.15	B 6	22 0.87	17 0.67	30 1.18	36 1.42	32 1.26	10 0.39	13 0.51	14 0.55	15 0.59	56 2.20	55 2.17	105 4.13	26 1.02	22 0.87
100 3.94	B 8	24 0.94	21 0.83	34 1.34	40 1.57	37 1.46	10 0.39	15 0.59	16 0.63	20 0.79	65 2.56	62 2.44	128 5.04	28 1.10	23 0.91
130 5.12	B 10	28 1.10	25 0.98	40 1.57	49 1.93	44 1.73	14 0.55	20 0.79	15 0.59	20 0.79	65 2.56	71 2.80	162 6.38	30 1.18	23 0.91
160 6.30	B 10	34 1.34	27 1.06	45 1.77	55 2.17	49 1.93	15 0.59	23 0.91	17 0.67	20 0.79	80 3.15	79 3.11	198 7.80	30 1.18	26 1.02
212 8.35	B 12	40 1.57	31 1.22	50 1.97	60 2.36	53 2.09	15 0.59	26 1.02	20 0.79	23 0.91	90 3.54	87 3.43	252 9.92	30 1.18	28 1.10

Specification

- Crank body
Plastic
Technopolymer (Polyamide PA)
- Special glass fiber reinforced
- Temperature resistant up to 194 °F (90 °C)
- Black, matte finish
- Hub bushing
Steel, blackened finish
- Retractable handle
Plastic
Technopolymer
- Black, matte finish
- Retractable mechanism
Steel, blackened finish
- Cross Holes GN 110 → page 2042
- Square Bores DIN 79 → page 2044
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Other modifications such as inch and special metric bores, keyways, set screw holes, etc.

Information

EN 570.6 crank handles with retractable hand piece are for applications where the hand piece must not protrude.

In the operating position, the hand piece is firmly locked. By pulling the hand piece in the axial direction out of its locating cone, it can be folded back into place.

The spring holds the hand piece firmly in both positions.

The structure of the crank arm and special technopolymer used make this handle very strong and therefore suitable for heavy duty work.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Crank Handles GN 471.3 → page 301
- Crank Handles GN 472.3 → page 302
- Crank Handles EN 570.2 → www.jwwinco.com
- Crank Handles EN 570.3 → www.jwwinco.com

How to order	1	Length l_1
	2	Blind bore d_1
EN 570.6-130-B10		

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4