


Metric



elesa
Original design BT-AV-B

3 Type

E With tapped blind bore



Metric table

Dimensions in: millimeters / inches

1 d_1	2 d_2	d_3	h	k	t min.	Drive SL for slotted screwdriver
12 0.47	M 3 M 4 M 5	9.5 0.37	12 0.47	8 0.31	6 0.24	SL 6.5
16 0.63	M 3 M 4 M 5	11 0.43	13.5 0.53	8.5 0.33	6 0.24	SL 6.5
20 0.79	M 5 M 6 -	11.5 0.45	16 0.63	10 0.39	6 0.24	SL 10

Specification

Knob

- Plastic, polyamide (PA)
- Reinforced
- Operating temperature
-22 °F to +266 °F (-30 °C to +130 °C)
- Black, matte finish

Insert

Brass **MS**
RoHS

Knurled nuts EN 592 are used for quick, tool-free mounting or adjusting of fixtures and devices.

If higher tightening or loosening torques are required, the slot can be used to drive the nut with a screwdriver.

see also...

	Page
EN 592 Knurled Screws (Steel Threaded Stud)	QVX
EN 530 Knurled Nuts (Phenolic Resin)	QVX
EN 590.5 Knurled Nuts (Stainless Steel Insert)	QVX
GN 420 Hollow Knurled Nuts (Steel Insert, Zinc Plated)	QVX

Technical Information

Plastic Characteristics	QVX
-------------------------	-----

How to order

1 **2** **3** **4**
EN 592-20-M5-E-MS

- 1** Handle diameter d_1
- 2** Thread d_2
- 3** Type
- 4** Material

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

