




elesa
Original design BT-HP-AV

SS Stainless Steel

Metric table

Dimensions in: millimeters / inches													
d₁	d₂	l₁	a₁ min. ... max.	a₂ min. ... max.	a₃ min. ... max.	d₃	d₄	d₅	h	k	l₂	l₃	Drive SL for slotted screwdriver
12 0.47	M 4	14 0.55	2...2 0.08...0.08	2...9 0.08...0.35	9...9 0.35...0.35	9.5 0.37	3.1 0.12	4.5 0.18	13 0.51	9 0.35	5 0.20	2 0.08	SL 6.5
12 0.47	M 4	20 0.79	2...8 0.08...0.31	8...9 0.31...0.35	9...15 0.35...0.59	9.5 0.37	3.1 0.12	4.5 0.18	13 0.51	9 0.35	5 0.20	2 0.08	SL 6.5
16 0.63	M 4	14 0.55	2...2 0.08...0.08	2...9 0.08...0.35	9...9 0.35...0.35	9.5 0.43	3.1 0.12	4.5 0.18	14 0.55	9 0.35	5 0.20	2 0.08	SL 6.5
16 0.63	M 4	20 0.79	2...8 0.08...0.31	8...9 0.31...0.35	9...15 0.35...0.59	11 0.43	3.1 0.12	4.5 0.18	14 0.55	9 0.35	5 0.20	2 0.08	SL 6.5
16 0.63	M 5	18 0.71	2.5...4 0.10...0.16	4...10,5 0.16...0.41	10.5...12 0.41...0.59	11 0.43	4 0.16	5.5 0.22	14 0.55	9 0.35	6 0.24	2.5 0.10	SL 6.5
16 0.63	M 5	24 0.94	4...10 0.16...0.39	10...12 0.39...0.47	12...18 0.59...0.71	11 0.43	4 0.16	5.5 0.22	14 0.55	9 0.35	6 0.24	2.5 0.10	SL 6.5
20 0.79	M 5	18 0.71	2.5...4 0.10...0.16	4...10,5 0.16...0.41	10.5...12 0.41...0.59	11 0.43	4 0.16	5.5 0.22	17 0.67	11 0.43	6 0.24	2.5 0.10	SL 10
20 0.79	M 5	24 0.94	4...10 0.16...0.39	10...12 0.39...0.47	12...18 0.59...0.71	11 0.43	4 0.16	5.5 0.22	17 0.67	11 0.43	6 0.24	2.5 0.10	SL 10
20 0.79	M 6	22 0.87	2.5...4 0.10...0.16	4...10,5 0.16...0.41	10.5...12 0.41...0.59	11 0.43	4.7 0.19	5.5 0.22	17 0.67	11 0.43	8 0.31	3 0.12	SL 10
20 0.79	M 6	32 1.26	4...10 0.16...0.39	10...12 0.39...0.47	12...18 0.59...0.71	11 0.43	4.7 0.19	6.5 0.26	17 0.67	11 0.43	8 0.31	3 0.12	SL 10

Specification

Knob Plastic, polyamide (PA) • Reinforced • Operating temperature -22 °F to +266 °F (-30 °C to +130 °C) • Black, matte finish		
Threaded stud • Steel Zinc plated, blue passivated finish • Stainless steel AISI 304	ST NI	
see also...	EN 591.2 Knurled Screws	Page QVX

RoHS

Technical Information

Plastic Characteristics QVX

Stainless Steel Characteristics QVX

How to order

1

Handle diameter d_1

2

Thread d_2

3

Length l_1

4

Material

EN 592.2-16-M5-24-NI