



4 Type

- A Without finger molding
- B With finger molding

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Thread	3 l ₁	b	d ₃	l ₂
13.5 0.53	M 4	20 0.79	11 0.43	11 0.43	8 0.31
13.5 0.53	M 5	20 0.79	11 0.43	11 0.43	10 0.39
16 0.63	M 5	23 0.91	13 0.51	12.5 0.49	10 0.39

Specification

- Plastic
Technopolymer (Polyamide PA)
- Temperature resistant up to 176 °F (80 °C)
- Black, matte finish
- Threaded spindle
Steel, zinc plated
- Plastic Characteristics → page QVX
- RoHS compliant

Information

EN 595 mini revolving handles are used, for example, in connection with small handwheels or cranked handles with low adjustment torque. Finger moldings in Type B provide additional safety against slipping and make operation easier.

<p>How to order</p> <p>EN 595-13.5-M5-20-A</p>	1	Handle diameter d ₁
	2	Thread d ₂
	3	Length l ₁
	4	Type