



Metric



elesa
Original design BT-AV-p

Metric table

Dimensions in: millimeters / inches

1 d ₁	2 d ₂	3 Length l			d ₃	h	k	Drive SL for slotted screwdriver
12 0.47	M 3	6 0.24	10 0.39	-	9.5 0.37	12 0.47	8 0.31	SL 6.5
12 0.47	M 4	6 0.24	10 0.39	-	9.5 0.37	12 0.47	8 0.31	SL 6.5
12 0.47	M 5	10 0.39	16 0.63	-	9.5 0.37	12 0.47	8 0.31	SL 6.5
16 0.63	M 3	6 0.24	10 0.39	-	11 0.43	13.5 0.53	8.5 0.33	SL 6.5
16 0.63	M 4	6 0.24	10 0.39	16 0.63	11 0.43	13.5 0.53	8.5 0.33	SL 6.5
16 0.63	M 5	10 0.39	16 0.63	-	11 0.43	13.5 0.53	8.5 0.33	SL 6.5
20 0.79	M 5	10 0.39	16 0.63	20 0.79	11 0.43	16 0.63	10 0.39	SL 10
20 0.79	M 6	10 0.39	16 0.63	25 0.98	11 0.43	16 0.63	10 0.39	SL 10

Specification

Knob

- Plastic, polyamide (PA)
- Reinforced
- Operating temperature
-22 °F to +266 °F (-30 °C to +130 °C)
- Black, matte finish

Threaded stud

- Steel
- Zinc plated, blue passivated finish

ST

RoHS

Knurled screws EN 592 are used for quick, tool-free mounting or adjusting of fixtures and devices. If higher tightening or loosening torques are required, the slot can be used to drive the screw with a screwdriver.

see also...

	Page
EN 592 Knurled Nuts (Brass Insert)	QVX
EN 529 Knurled Screws (Phenolic Resin)	QVX
EN 591.5 Knurled Screws (Stainless Steel Threaded Stud)	QVX
GN 421 Hollow Knurled Screws (Steel, Zinc Plated Threaded Stud)	QVX

Technical Information

Plastic Characteristics

QVX

How to order

1	Handle diameter d ₁
2	Thread d ₂
3	Length l
4	Material (Threaded stud)

EN 592-12-M4-10-ST

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

