



**Specification**



- Lever body / serrated insert  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 265 °F (130 °C)  
- Black-gray, similar to RAL 7021, matte finish
- Color of the push button (shiny finish):
 

● DSG
● DOR
● DGR
● DGB
● DBL
● DRT
● DGN
- Threaded stud  
Steel, zinc plated, blue passivated finish
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

**Information**

EN 600 straight adjustable levers are renowned for their style and ergonomic shape. Like all adjustable levers, they are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged. Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage. Resistant to solvents, oils, grease and other chemical agents.

see also...

- *Product Family Ergostyle®* → page QVX
- *Adjustable Levers EN 603 (with Push Button)* → page QVX

**On request**

- With stainless steel threaded stud

How to order	
1	Lever length $l_1$
2	Thread $d_1$
3	Thread length $l_2$
4	Color of the push button

**EN 600-1.18-10X24-0.500-DOR**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4



**Inch table**

Dimensions in: inches - *millimeters*

<b>1</b>	<b>2</b>	<b>3</b>							<b>d<sub>2</sub></b>	<b>d<sub>3</sub></b>	<b>h<sub>1</sub></b>	<b>h<sub>2</sub></b>	<b>h<sub>3</sub></b>	<b>h<sub>4</sub></b>
<b>l<sub>1</sub></b>	<b>d<sub>1</sub></b>	<b>l<sub>2</sub></b>												<b>h<sub>4</sub></b>
														<b>Stroke</b>
1.18 30.0	10 x 24	0.500 12.7	0.625 15.9	0.750 19.1	1.000 25.4	-	-	-	0.47 11.9	0.61 15.5	1.16 29.5	0.24 6.1	1.06 26.9	0.14 3.6
1.18 30.0	10 x 32	0.500 12.7	0.750 19.1	-	-	-	-	-	0.47 11.9	0.61 15.5	1.16 29.5	0.24 6.1	1.06 26.9	0.14 3.6
1.18 30.0	1/4 x 20	0.500 12.7	0.625 15.9	0.750 19.1	1.000 25.4	1.500 38.1	-	-	0.47 11.9	0.61 15.5	1.16 29.5	0.24 6.1	1.06 26.9	0.14 3.6
1.73 43.9	10 x 24	0.500 12.7	0.625 15.9	0.750 19.1	1.000 25.4	-	-	-	0.47 11.9	0.61 15.5	1.16 29.5	0.24 6.1	1.06 26.9	0.14 3.6
1.73 43.9	10 x 32	0.500 12.7	0.750 19.1	-	-	-	-	-	0.47 11.9	0.61 15.5	1.16 29.5	0.24 6.1	1.06 26.9	0.14 3.6
1.73 43.9	1/4 x 20	0.500 12.7	0.625 15.9	0.750 19.1	1.000 25.4	1.500 38.1	-	-	0.47 11.9	0.61 15.5	1.16 29.5	0.24 6.1	1.06 26.9	0.14 3.6
2.48 63.0	1/4 x 20	0.500 12.7	0.625 15.9	0.750 19.1	1.000 25.4	1.250 31.8	1.500 38.1	-	0.59 15.0	0.75 19.1	1.48 37.6	0.31 7.9	1.44 36.6	0.14 3.6
2.48 63.0	5/16 x 18	0.500 12.7	0.625 15.9	0.750 19.1	1.000 25.4	1.250 31.8	1.500 38.1	2.000 50.8	0.59 15.0	0.75 19.1	1.48 37.6	0.31 7.9	1.44 36.6	0.14 3.6
2.48 63.0	3/8 x 16	0.750 19.1	1.250 31.8	-	-	-	-	-	0.59 15.0	0.75 19.1	1.48 37.6	0.31 7.9	1.44 36.6	0.14 3.6
3.07 78.0	3/8 x 16	0.750 19.1	1.000 25.4	1.250 31.8	1.500 38.1	2.000 50.8	2.500 63.5	-	0.75 19.1	0.96 24.4	1.85 47.0	0.41 10.5	1.69 43.0	0.14 3.6
3.07 78.0	1/2 x 13	1.250 31.8	1.500 38.1	2.000 50.8	-	-	-	-	0.75 19.1	0.96 24.4	1.85 47.0	0.41 10.5	1.69 43.0	0.14 3.6

**Metric table**

Dimensions in: millimeters - *inches*

<b>1</b>	<b>2</b>	<b>3</b>							<b>d<sub>2</sub></b>	<b>d<sub>3</sub></b>	<b>h<sub>1</sub></b>	<b>h<sub>2</sub></b>	<b>h<sub>3</sub></b>	<b>h<sub>4</sub></b>			
<b>l<sub>1</sub></b>	<b>d<sub>1</sub></b>	<b>l<sub>2</sub></b>												<b>h<sub>4</sub></b>			
														<b>Stroke</b>			
30 1.18	M 5	10 0.39	16 0.63	20 0.79	-	-	-	-	-	-	12 0.47	15.5 0.61	29.5 1.16	6 0.24	27 1.06	3.5 0.14	
30 1.18	M 6	10 0.39	16 0.63	20 0.79	25 0.98	30 1.18	40 1.57	-	-	-	12 0.47	15.5 0.61	29.5 1.16	6 0.24	27 1.06	3.5 0.14	
44 1.73	M 5	10 0.39	16 0.63	20 0.79	-	-	-	-	-	-	12 0.47	15.5 0.61	29.5 1.16	6 0.24	27 1.06	3.5 0.14	
44 1.73	M 6	10 0.39	16 0.63	20 0.79	25 0.98	30 1.18	40 1.57	45 1.77	-	-	12 0.47	15.5 0.61	29.5 1.16	6 0.24	27 1.06	3.5 0.14	
63 2.48	M 6	10 0.39	16 0.63	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	-	-	15 0.59	19 0.75	37.5 1.48	8 0.31	36.5 1.44	3.5 0.14	
63 2.48	M 8	16 0.63	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	45 1.77	50 1.97	60 2.36	70 2.76	15 0.59	19 0.75	37.5 1.48	8 0.31	36.5 1.44	3.5 0.14
78 3.07	M 8	20 0.79	25 0.98	30 1.18	40 1.57	45 1.77	50 1.97	55 2.17	60 2.36	70 2.76	-	19 0.75	24.5 0.96	47 1.85	10.5 0.41	43 1.69	3.5 0.14
78 3.07	M 10	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	50 1.97	60 2.36	70 2.76	-	-	19 0.75	24.5 0.96	47 1.85	10.5 0.41	43 1.69	3.5 0.14
78 3.07	M 12	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	45 1.77	50 1.97	60 2.36	70 2.76	80 3.15	19 0.75	24.5 0.96	47 1.85	10.5 0.41	43 1.69	3.5 0.14