



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$ Thread	$d_3$	$d_4 + 0.5$	$l_1$	$l_2$	$l_3 \approx$	$l_4 \approx$
45 1.77	M 10	12 0.47	32 1.26	64 2.52	17 0.67	1 0.04	22 0.87

**Specification**

- Plastic  
Technopolymer (Polypropylene PP)  
- Temperature resistant up to 175 °F (80 °C)  
- Black, matte finish
- Threaded stud  
Steel, zinc plated, blue passivated finish
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

**Information**

EN 596 revolving ball knobs are used in applications that require friction-free turning action, such as vertically positioned handwheels or cranked handles.

see also...

- *Product Family Ergostyle®* → page QVX

**How to order**

<sup>1</sup> <sup>2</sup>  
**EN 596-45-M10**

- <sup>1</sup> Ball diameter  $d_1$
- <sup>2</sup> Thread  $d_2$