



Metric table

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub> +0.5	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub> ≈	l <sub>4</sub> ≈
45 1.77	M 10	12 0.47	32 1.26	64 2.52	17 0.67	1 0.04	22 0.87

Specification

- Plastic  
Technopolymer (Polypropylene PP)  
- Temperature resistant up to 175 °F (80 °C)  
- Black, matte finish
- Threaded stud  
Steel, zinc plated, blue passivated finish
- Plastic Characteristics → page QVX
- RoHS compliant

Information

EN 596 revolving ball knobs are used in applications that require friction-free turning action, such as vertically positioned handwheels or cranked handles.

see also...

- Product Family Ergostyle® → page QVX

How to order <sup>1</sup> <sup>2</sup> <b>EN 596-45-M10</b>	1 Ball diameter d <sub>1</sub>
	2 Thread d <sub>2</sub>