


Type A / Type B



Type E



SS Stainless Steel

4 Type

- A** With stainless steel threaded spindle
- B** With steel threaded spindle
- E** Without threaded spindle

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 230 °F (110 °C)
- Black, shiny finish
- Threaded spindle
- Type **A**:
Stainless steel AISI 304
- Type **B**:
Steel, matte chrome plated finish
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**



KU

Information

The outstanding feature of EN 598.2 revolving handles is their highly robust design. They are resistant to solvents, oils, grease and other chemical agents.

Type E is suitable for use with user-specific threaded spindle.

see also...

- *Revolving Handles GN 598.1 (with Stainless Steel Threaded Spindle)* → page 39

How to order (Inch, with threaded spindle)	1 Material
EN 598.2-KU-18-1/4X20-B	2 Handle diameter d ₁
	3 Thread d ₂
	4 Type
How to order (Metric, without threaded spindle)	1 Material
EN 598.2-KU-26-13-E	2 Handle diameter d ₁
	3 Bore diameter d ₃
	4 Type

Inch table

Dimensions in: inches - *millimeters*

² d ₁	³ d ₂ Type B	d ₄	d ₅	l ₁	l ₂	l ₃	l ₄	l ₅	A/F in mm
0.71 18	1/4 x 20*	0.59 15	0.47 12	1.57 40	0.51 13	0.04 1	1.54 39	1.38 35	4
0.83 21	5/16 x 18*	0.67 17	0.55 14	1.97 50	0.59 15	-	1.97 50	1.69 43	5
0.91 23	5/16 x 18*	0.75 19	0.63 16	2.56 65	0.67 17	0.04 1	2.52 64	2.20 56	6
1.02 26	3/8 x 16*	0.83 21	0.67 17	3.15 80	0.71 18	0.04 1	3.11 79	2.76 70	6
1.10 28	3/8 x 16*	0.87 22	0.75 19	3.54 90	0.71 18	0.04 1	3.50 89	3.11 79	8

* Inch sizes are only available with steel threaded spindle

Metric table

Dimensions in: millimeters - *inches*

² d ₁	³ d ₂ 6g Type A, Type B	³ d ₃ ^{+0.3} / _{-0.1} Type E	d ₄	d ₅	l ₁	l ₂	l ₃	l ₄	l ₅	A/F	
18 0.71	M 6	-	8 0.31	15 0.59	12 0.47	40 1.57	13 0.51	1 0.04	39 1.54	35 1.38	4
21 0.83	M 8	-	10 0.39	17 0.67	14 0.55	50 1.97	15 0.59	-	50 1.97	43 1.69	5
23 0.91	M 8	-	12 0.47	19 0.75	16 0.63	65 2.56	17 0.67	1 0.04	64 2.52	56 2.20	6
23 0.91	M 10	-	12 0.47	19 0.75	16 0.63	65 2.56	17 0.67	1 0.04	64 2.52	56 2.20	6
26 1.02	M 10	-	13 0.51	21 0.83	17 0.67	80 3.15	18 0.71	1 0.04	79 3.11	70 2.76	6
28 1.10	M 10	-	14 0.55	22 0.87	19 0.75	90 3.54	18 0.71	1 0.04	89 3.50	79 3.11	8
31 1.22	M 12	M 14	16 0.63	25 0.98	20 0.79	102 4.02	20 0.79	2 0.08	100 3.94	89 3.50	8

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

