



Inch | Metric



**elesa**  
Original design ERX.



**Specification**



**Lever body**

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -22 °F to +266 °F (-30 °C to +130 °C)
- Black-gray, matte finish, similar to RAL 7021

**Tapped insert**

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Black
- Tapped insert Brass

**Push button**

- Plastic, Polyamide (PA)
- Black-gray, RAL 7021, shiny finish
- Orange, RAL 2004, shiny finish
- Gray, RAL 7035, shiny finish
- Yellow, RAL 1021, shiny finish
- Blue, RAL 5024, shiny finish
- Red, RAL 3000, shiny finish
- Green, RAL 6017, shiny finish

- **DSG**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**
- **DGN**

RoHS

The slightly arched ergonomic shape of the adjustable levers EN 603 gives the operator a comfortable and safe grip, while the thumb rests naturally on the push button.

These levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the mating serrations of the lever and the insert automatically re-engage via a spring and push button that holds the assembly together.

Resistant to solvents, oils, grease and other chemical agents.

**see also...**

	Page
<b>EN 603.1</b> Adjustable Levers (Plastic, with Stainless Steel Tapped Insert, with Push Button)	QVX
<b>EN 603.4</b> Adjustable Levers (with Brass Tapped Insert, with Push Button, Chrome-Plated)	QVX
<b>EN 600</b> Straight Adjustable Levers (Plastic, with Brass Insert, with Push Button)	QVX

**Technical Information**

Product Family Ergostyle®	QVX
Plastic Characteristics	QVX

How to order (Inch)

**EN 603-44-10X32-DSG**

- 1 Lever length  $l_1$
- 2 Thread  $d_1$
- 3 Color of the push button

How to order (Metric)

**EN 603-95-M12-DOR**

- 1 Lever length  $l_1$
- 2 Thread  $d_1$
- 3 Color of the push button

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4



## Inch table

1

2

Dimensions in: inches / millimeters

<b>l<sub>1</sub></b>	<b>d<sub>1</sub></b>				<b>d<sub>2</sub></b>	<b>d<sub>3</sub></b>	<b>h<sub>1</sub></b>	<b>h<sub>2</sub></b>	<b>h<sub>3</sub></b>	<b>h<sub>4</sub></b> Stroke	<b>t</b> min.
1.73 44	10 x 24	10 x 32	1/4 x 20		0.47 12	0.61 15.5	1.16 29.5	0.24 6	1.28 32.5	0.14 3.5	0.39 10
2.48 63	1/4 x 20	-	-		0.59 15	0.75 19	1.48 37.5	0.31 8	1.69 43	0.16 4	0.47 12
2.48 63	5/16 x 18	-	-		0.59 15	0.75 19	1.48 37.5	0.31 8	1.69 43	0.16 4	0.51 13
3.07 78	3/8 x 16	1/2 x 13	-		0.75 19	0.91 23	1.85 47	0.47 12	2.13 54	0.16 4	0.67 17
3.74 95	3/8 x 16	1/2 x 13	-		0.85 21.5	1.04 26.5	2.15 54.5	0.51 13	2.54 64.5	0.18 4.5	0.79 20

## Metric table

1

2

Dimensions in: millimeters / inches

<b>l<sub>1</sub></b>	<b>d<sub>1</sub></b>				<b>d<sub>2</sub></b>	<b>d<sub>3</sub></b>	<b>h<sub>1</sub></b>	<b>h<sub>2</sub></b>	<b>h<sub>3</sub></b>	<b>h<sub>4</sub></b> Stroke	<b>t</b> min.
30 1.18	M 3	M 4	M 5	M 6	12 0.47	15.5 0.61	29.5 1.16	6 0.24	30 1.18	3.5 0.14	10 0.39
44 1.73	M 5	M 6	-	-	12 0.47	15.5 0.61	29.5 1.16	6 0.24	32.5 1.28	3.5 0.14	10 0.39
63 2.48	M 6	M 8	M 10	-	15 0.59	19 0.75	37.5 1.48	8 0.31	43 1.69	4 0.16	13 0.51
78 3.07	M 8	M 10	M 12	-	19 0.75	23 0.91	47 1.85	12 0.47	54 2.13	4 0.16	17 0.67
95 3.74	M 10	M 12	M 14	-	21.5 0.85	26.5 1.04	54.5 2.15	13 0.51	64.5 2.54	4.5 0.18	20 0.79
108 4.25	M 12	M 14	M 16	-	25 0.98	30 1.18	54.5 2.15	11 0.43	65.5 2.58	4.5 0.18	20 0.79