Adjustable Levers

Zinc Die-Cast, Threaded Stud Type, with SST Components, Ergostyle®





Inch | Metric

elesa

Original design ERM.SST-p

Specification

Lever body
Zinc die-cast
Powder coated

• Black, RAL 9005, textured finish	**SW**
• Orange, RAL 2004, textured finish	**OS**
• Red, RAL 3000, textured finish	**RS**
• Silver, RAL 9006, textured finish	**SR**

Threaded stud / Retaining screw
Stainless steel AISI 303

RoHS

On request

• Special stud lengths

Adjustable levers EN 602.1 have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.
Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.
The slightly arched shape of the lever gives the operator a comfortable and safe grip and makes the design more elegant.

see also...	Page
EN 602 Adjustable Levers (Zinc Die-Cast, with Steel Threaded Stud)	QVX
EN 604.1 Adjustable Levers (Plastic, Stainless Steel Threaded Stud)	QVX

Technical Information

Product Family Ergostyle®	QVX
Strength Values of Screws	QVX
Stainless Steel Characteristics	QVX

How to order (Inch)

EN 602.1-44-10X32-12-RS

1	Lever length l_1
2	Thread d_1
3	Thread length l_2
4	Color

How to order (Metric)

EN 602.1-78- M12 -40-SR

1	Lever length l_1
2	Thread d_1
3	Thread length l_2
4	Color

⚠ WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov

Inch table

Dimensions in: inches / millimeters

l_1	d_1	l_2								d_2	d_3	h_1	h_2	h_3	h_4 Stroke
1.73 44	10 x 32	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.14 3.5	1.18 30	0.14 3.5
1.73 44	10 x 24	0.63 16	-	-	-	-	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.14 3.5	1.18 30	0.14 3.5
1.73 44	1/4 x 20	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	0.39 10	0.57 14.5	0.96 24.5	0.14 3.5	1.18 30	0.14 3.5
2.48 63	5/16 x 18	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.53 13.5	0.71 18	1.22 31	0.14 3.5	1.50 38	0.16 4
2.48 63	3/8 x 16	0.79 20	0.98 25	1.26 32	1.57 40	-	-	-	-	0.53 13.5	0.71 18	1.22 31	0.14 3.5	1.50 38	0.16 4
3.07 78	3/8 x 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.63 16	0.85 21.5	1.42 36	0.14 3.5	1.81 46	0.16 4
3.07 78	1/2 x 13	0.79 20	0.98 25	1.26 32	1.57 40	1.97 50	-	-	-	0.63 16	0.85 21.5	1.42 36	0.14 3.5	1.81 46	0.16 4
3.74 95	1/2 x 13	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	-	0.75 19	0.98 25	1.69 43	0.20 5	2.20 56	0.16 4

Metric table

Dimensions in: millimeters / inches

l_1	d_1			l_2							d_2	d_3	h_1	h_2	h_3	h_4 Stroke
44 1.73	M 4	-	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	10 0.39	14.5 0.57	24.5 0.96	3.5 0.14	30 1.18	3.5 0.14
44 1.73	M 5	M 6	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	14.5 0.57	24.5 0.96	3.5 0.14	30 1.18	3.5 0.14
63 2.48	M 6	M 8	-	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	18 0.71	31 1.22	3.5 0.14	38 1.50	4 0.16
78 3.07	M 8	M 10	M 12	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 0.63	21.5 0.85	36 1.42	3.5 0.14	46 1.81	4 0.16
95 3.74	M 10	M 12	-	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	19 0.75	25 0.98	43 1.69	5 0.20	56 2.20	4 0.16

WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov