



Specification



- Lever body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black-gray, RAL 7021, matte finish ● **SG**
- Serrated inlay
Zinc die-cast
- Threaded stud / retaining screw
Stainless steel AISI 303
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

On request

- Lever body
Orange, RAL 2004, matte finish ● **OR**

Information

EN 604.1 adjustable levers like all the products of the Ergostyle® product family are renowned for their good style and also their ergonomical shape. The gently arched handle with a reinforced end of the lever gives the operator a good grip.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- *Product Family Ergostyle®* → page 18

How to order (Inch)	1	Lever length l_1
	2	Thread d_1
	3	Thread length l_2
	4	Color
EN 604.1-44-1/4X20-16-SG		

How to order (Metric)	1	Lever length l_1
	2	Thread d_1
	3	Thread length l_2
	4	Color
EN 604.1-95-M12-25-SG		

Inch table

Dimensions in: inches - *millimeters*

¹ l ₁	² d ₁	³ l ₂							d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ Stroke
1.73 44	1/4 x 20	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	0.39 10	0.61 15.5	0.96 24.5	0.14 3.5	1.20 30.5	0.14 3.5	
2.48 63	5/16 x 18	0.79 20	1.26 32	1.57 40	2.48 63	-	-	0.53 13.5	0.75 19	1.22 31	0.14 3.5	1.52 38.5	0.16 4	
2.48 63	3/8 x 16	0.79 20	1.57 40	-	-	-	-	0.53 13.5	0.75 19	1.22 31	0.14 3.5	1.52 38.5	0.16 4	
3.07 78	3/8 x 16	0.98 25	1.26 32	1.57 40	1.97 50	2.48 63	-	0.63 16	0.91 23	1.42 36	0.14 3.5	1.83 46.5	0.16 4	
3.74 95	1/2 x 13	1.26 32	1.97 50	2.48 63	-	-	-	0.75 19	1.04 26.5	1.69 43	0.20 5	2.22 56.5	0.16 4	

Metric table

Dimensions in: millimeters - *inches*

¹ l ₁	² d ₁	³ l ₂							d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	
44 1.73	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	15.5 0.61	24.5 0.96	3.5 0.14	30.5 1.20	3.5 0.14
63 2.48	M 6	M 8	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	19 0.75	31 1.22	3.5 0.14	38.5 1.52	4 0.16
78 3.07	M 8	M 10	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 0.63	23 0.91	36 1.42	3.5 0.14	46.5 1.83	4 0.16
95 3.74	M 10	M 12	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	19 0.75	26.5 1.04	43 1.69	5 0.20	56.5 2.22	4 0.16

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

