




Metric table

1

2

Dimensions in: millimeters / inches

l_1	d_1	d_2	d_3	h_1	h_2	h_3	h_4 Stroke	t min.
44 1.73	M 6	12 0.47	15.5 0.61	29.5 1.16	6 0.24	32.5 1.28	3.5 0.14	10 0.39
63 2.48	M 8	15 0.59	19 0.75	37.5 1.48	8 0.31	43 1.69	4 0.16	13 0.51
78 3.07	M 10	19 0.75	23 0.91	47 1.85	12 0.47	54 2.13	4 0.16	17 0.67
95 3.74	M 12	21.5 0.85	26.5 1.04	54.5 2.15	13 0.51	64.5 2.54	4.5 0.18	20 0.79

Specification

- Lever body

Plastic, Polyamide (PA)
 - Glass fiber reinforced
 - Operating temperature -22 °F to +176 °F (-30 °C to +80 °C)
 - Chrome plated, shiny finish
- Push button

Black, shiny finish
- Serrated insert

Plastic, Polyamide (PA)
 - Glass fiber reinforced
 - Black
 - Tapped insertBrass
- RoHS
- On request

- With threaded stud

The slightly arched ergonomic shape of the adjustable levers EN 603.4 gives the operator a comfortable and safe grip, while the thumb rests naturally on the push button.

These levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the mating serrations of the lever and the insert automatically re-engage via a spring and push button that holds the assembly together.

Resistant to solvents, oils, grease and other chemical agents.

see also...	Page
EN 603 Adjustable Levers (Brass Insert, with Push Button)	QVX

Technical Information	
Product Family Ergostyle®	QVX
Plastic Characteristics	QVX

How to order	1 Lever length l_1
EN 603.4-95-M12	2 Thread d_1