Adjustable Levers

Plastic, Threaded Stud Type, with Steel Components, Ergostyle®





Inch | Metric

elesa
Original design ERZ.p

Specification

Lever body
Plastic, (Polyamide PA)
- Glass fiber reinforced
- Operating temperature
  -22 °F to +266 °F (-30 °C to +130 °C)
- Black-gray, RAL 7021, matte finish ● **SG**

Serrated inlay
Zinc die-cast

Threaded stud / Retaining screw
Steel
- Blackened finish
- Property class 5.8

RoHS

On request

- Lever body
  Orange, RAL 2004, matte finish ● **OR**

Adjustable levers EN 604 like all the products of the Ergostyle® product family are renowned for their good style and also their ergonomical shape. The gently arched handle with a reinforced end of the lever gives the operator a good grip.
Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...	Page
EN 604.1 Adjustable Levers (Plastic, with Stainless Steel Threaded Stud)	QVX
EN 602 Adjustable Levers (Zinc Die-Cast, with Steel Threaded Stud)	QVX

Technical Information

Product Family Ergostyle®	QVX
Strength Values of Screws	QVX
Plastic Characteristics	QVX

How to order (Inch)

EN 604-44-10X32-12-SG

1	Lever length l_1
2	Thread d_1
3	Thread length l_2
4	Color

How to order (Metric)

EN 604-95-M12-25-SG

1	Lever length l_1
2	Thread d_1
3	Thread length l_2
4	Color

⚠ WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov

Inch table

Dimensions in: inches / millimeters

l_1	d_1	l_2									d_2	d_3	h_1	h_2	h_3	h_4 Stroke
1.73 44	10 x 32	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	-	0.39 10	0.61 15.5	0.96 24.5	0.14 3.5	1.20 30.5	0.14 3.5
1.73 44	1/4 x 20	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	-	0.39 10	0.61 15.5	0.96 24.5	0.14 3.5	1.20 30.5	0.14 3.5
2.48 63	5/16 x 18	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.53 13.5	0.75 19	1.22 31	0.14 3.5	1.52 38.5	0.16 4
2.48 63	3/8 x 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	-	-	-	0.53 13.5	0.75 19	1.22 31	0.14 3.5	1.52 38.5	0.16 4
3.07 78	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.63 16	0.91 23	1.42 36	0.14 3.5	1.83 46.5	0.16 4
3.74 95	3/8 x 16	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	-	-	0.75 19	1.04 26.5	1.69 43	0.20 5	2.22 56.5	0.16 4
3.74 95	1/2 x 13	0.98 25	1.26 32	1.38 35	1.57 40	1.77 45	1.97 50	2.48 63	-	-	0.75 19	1.04 26.5	1.69 43	0.20 5	2.22 56.5	0.16 4

Metric table

Dimensions in: millimeters / inches

l_1	d_1		l_2								d_2	d_3	h_1	h_2	h_3	h_4 Stroke
44 1.73	M 4	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	10 0.39	15.5 0.61	24.5 0.96	3.5 0.14	30.5 1.20	3.5 0.14
44 1.73	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	10 0.39	15.5 0.61	24.5 0.96	3.5 0.14	30.5 1.20	3.5 0.14
63 2.48	M 6	M 8	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	19 0.75	31 1.22	3.5 0.14	38.5 1.52	4 0.16
63 2.48	M 10	-	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	13.5 0.53	19 0.75	31 1.22	3.5 0.14	38.5 1.52	4 0.16
78 3.07	M 8	M 10	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 0.63	23 0.91	36 1.42	3.5 0.14	46.5 1.83	4 0.16
78 3.07	M 12	-	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	16 0.63	23 0.91	36 1.42	3.5 0.14	46.5 1.83	4 0.16
95 3.74	M 10	M 12	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	19 0.75	26.5 1.04	43 1.69	5 0.20	56.5 2.22	4 0.16
95 3.74	M 16	-	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	19 0.75	26.5 1.04	43 1.69	5 0.20	56.5 2.22	4 0.16

WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov