



Inch table

Dimensions in: inches - millimeters

1	2								
$l_1$	$d_1$	$d_2$	$d_3$	$h_1$	$h_2$	$h_3$	$h_4$ Stroke	$t$ min.	
1.73 44	10 x 32 1/4 x 20	0.39 10	0.61 15.5	0.96 24.5	0.14 3.5	1.20 30.5	0.14 3.5	0.31 8	
2.48 63	1/4 x 20 5/16 x 18	0.53 13.5	0.75 19	1.22 31	0.14 3.5	1.52 38.5	0.16 4	0.39 10	
3.07 78	5/16 x 18 3/8 x 16	0.63 16	0.91 23	1.42 36	0.14 3.5	1.83 46.5	0.16 4	0.55 14	
3.74 95	3/8 x 16 1/2 x 13	0.75 19	1.04 26.5	1.69 43	0.20 5	2.22 56.5	0.16 4	0.67 17	

Metric table

Dimensions in: millimeters - inches

1	2								
$l_1$	$d_1$	$d_2$	$d_3$	$h_1$	$h_2$	$h_3$	$h_4$ Stroke	$t$ min.	
44 1.73	M 4 M 5 M 6	10 0.39	15.5 0.61	24.5 0.96	3.5 0.14	30.5 1.20	3.5 0.14	8 0.31	
63 2.48	M 6 M 8	- 13.5 0.53	- 19 0.75	- 31 1.22	- 3.5 0.14	- 38.5 1.52	- 4 0.16	- 10 0.39	
78 3.07	M 8 M 10	- 16 0.63	- 23 0.91	- 36 1.42	- 3.5 0.14	- 46.5 1.83	- 4 0.16	- 14 0.55	
95 3.74	M 10 M 12	- 19 0.75	- 26.5 1.04	- 43 1.69	- 5 0.20	- 56.5 2.22	- 4 0.16	- 17 0.67	

Specification

- Lever body  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 266 °F (130 °C)  
- Black-gray, RAL 7021, matte finish ● SG
- Serrated inlay  
Zinc die-cast
- Tapped insert / retaining screw  
Steel, blackened finish
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Lever body  
Orange, RAL 2004, matte finish ● OR

Information

EN 604 adjustable levers like all the products of the Ergostyle® product family are renowned for their good style and also their ergonomic shape. The gently arched handle with a reinforced end of the lever gives the operator a good grip.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- Product Family Ergostyle® → page 18
- Adjustable Levers EN 602 (Zinc Die-Cast, with Steel Insert) → page 486

How to order (Inch)	1	Lever length $l_1$
	2	Thread $d_1$
<b>EN 604-78-3/8X16-SG</b>	3	Color

How to order (Metric)	1	Lever length $l_1$
	2	Thread $d_1$
<b>EN 604-44-M6-SG</b>	3	Color