



**Specification**



- Lever body  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 266 °F (130 °C)  
- Black-gray, RAL 7021, matte finish ● **SG**
- Serrated inlay  
Zinc die-cast
- Threaded stud / retaining screw  
Steel  
- Blackened finish  
- Property class 5.8
- *Strength Values of Screws* → page 2127
- *Plastic Characteristics* → page 2135
- *RoHS compliant*

**On request**

- Lever body  
Orange, RAL 2004, matte finish ● **OR**

**Information**

EN 604 adjustable levers like all the products of the Ergostyle® product family are renowned for their good style and also their ergonomical shape. The gently arched handle with a reinforced end of the lever gives the operator a good grip.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- *Product Family Ergostyle®* → page 18
- *Adjustable Levers EN 602 (Zinc Die-Cast, with Steel Threaded Stud)* → page 488

How to order (Inch)	1 Lever length $l_1$
1 2 3 4	2 Thread $d_1$
<b>EN 604-44-10X32-12-SG</b>	3 Thread length $l_2$
	4 Color

How to order (Metric)	1 Lever length $l_1$
1 2 3 4	2 Thread $d_1$
<b>EN 604-95-M12-25-SG</b>	3 Thread length $l_2$
	4 Color

**Inch table**

Dimensions in: inches - *millimeters*

<sup>1</sup> l <sub>1</sub>	<sup>2</sup> d <sub>1</sub>	<sup>3</sup> l <sub>2</sub>									d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub> Stroke
1.73 44	10 x 32	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	-	0.39 10	0.61 15.5	0.96 24.5	0.14 3.5	1.20 30.5	0.14 3.5
1.73 44	1/4 x 20	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	-	0.39 10	0.61 15.5	0.96 24.5	0.14 3.5	1.20 30.5	0.14 3.5
2.48 63	5/16 x 18	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.53 13.5	0.75 19	1.22 31	0.14 3.5	1.52 38.5	0.16 4
2.48 63	3/8 x 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	-	-	-	0.53 13.5	0.75 19	1.22 31	0.14 3.5	1.52 38.5	0.16 4
3.07 78	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.63 16	0.91 23	1.42 36	0.14 3.5	1.83 46.5	0.16 4
3.74 95	3/8 x 16	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	-	-	0.75 19	1.04 26.5	1.69 43	0.20 5	2.22 56.5	0.16 4
3.74 95	1/2 x 13	0.98 25	1.26 32	1.38 35	1.57 40	1.77 45	1.97 50	2.48 63	-	-	0.75 19	1.04 26.5	1.69 43	0.20 5	2.22 56.5	0.16 4

**Metric table**

Dimensions in: millimeters - *inches*

<sup>1</sup> l <sub>1</sub>	<sup>2</sup> d <sub>1</sub>	<sup>3</sup> l <sub>2</sub>									d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub> Stroke
44 1.73	M 4	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	10 0.39	15.5 0.61	24.5 0.96	3.5 0.14	30.5 1.20	3.5 0.14
44 1.73	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	10 0.39	15.5 0.61	24.5 0.96	3.5 0.14	30.5 1.20	3.5 0.14
63 2.48	M 6	M 8	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	19 0.75	31 1.22	3.5 0.14	38.5 1.52	4 0.16
63 2.48	M 10	-	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	13.5 0.53	19 0.75	31 1.22	3.5 0.14	38.5 1.52	4 0.16
78 3.07	M 8	M 10	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 0.63	23 0.91	36 1.42	3.5 0.14	46.5 1.83	4 0.16
78 3.07	M 12	-	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	16 0.63	23 0.91	36 1.42	3.5 0.14	46.5 1.83	4 0.16
95 3.74	M 10	M 12	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	19 0.75	26.5 1.04	43 1.69	5 0.20	56.5 2.22	4 0.16
95 3.74	M 16	-	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	19 0.75	26.5 1.04	43 1.69	5 0.20	56.5 2.22	4 0.16

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

