


Application example



**SS** Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub> H12	d <sub>2</sub> -0.1	Length l ±0.1							For indexing plungers / cam action indexing plungers with thread Ø																										
		2	4	6	8	-	-	-	M 6	GN 414	GN 414.1	GN 607	GN 607.1	GN 514	GN 816	GN 816.1	GN 612.8	GN 617	GN 617.1	EN 617.2	GN 672	GN 717	GN 814	GN 817	GN 817.2	GN 817.6	GN 817.4	GN 817.8	GN 822	GN 822.1	GN 822.6	GN 822.7	GN 7336.8		
6 0.24	7 0.28	2 0.08	4 0.16	6 0.24	8 0.31	-	-	-	M 6	-	-	-	-	-	-	-	-	-	-	-	-	X	-	-	-	-	-	-	-	-	-	-	-	-	
8 0.31	10 0.39	2 0.08	4 0.16	6 0.24	8 0.31	10 0.39	-	-	M 8	-	-	-	-	-	-	-	-	-	-	-	-	X	-	X	-	-	-	X	-	-	-	-	-		
10 0.39	12 0.47	2 0.08	4 0.16	6 0.24	8 0.31	10 0.39	12 0.47	-	M 10	-	-	-	-	X	-	X	-	X	-	X	-	X	-	X	-	X	-	X	-	-	-	-	-	-	
12 0.47	14 0.55	2 0.08	4 0.16	6 0.24	8 0.31	10 0.39	12 0.47	14 0.55	M 12	-	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
12 0.47	17 0.67	2 0.08	4 0.16	5 0.20	6 0.24	8 0.31	10 0.39	12 0.47	M 12	X	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
16 0.63	17 0.67	2 0.08	4 0.16	6 0.24	8 0.31	10 0.39	12 0.47	-	M 16	-	X	-	-	-	-	-	-	X	-	X	-	X	-	X	-	X	-	X	-	X	-	X	-	-	
16 0.63	19 0.75	2 0.08	4 0.16	6 0.24	8 0.31	10 0.39	12 0.47	-	M 16	X	-	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
20 0.79	22 0.87	6 0.24	8 0.31	10 0.39	12 0.47	14 0.55	16 0.63	18 0.71	M 20	-	-	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X

**Specification**

- Spacer bushing  
Stainless steel AISI 303
- ISO Fundamental Tolerances → page 2129
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**Information**

GN 609.5 spacer bushings compensate for the body thread lengths on indexing plungers and cam action indexing plungers to allow mounting through walls of varying thicknesses.

<p>How to order</p> <p><b>GN 609.5-16-17-4</b></p>	1	Inner diameter d <sub>1</sub>
	2	Outer diameter d <sub>2</sub>
	3	Length l