



- 3 Type**
- A1** Through hole
 - A2** Through hole with continuous thread
 - A3** Through hole with thread on both sides

Metric table

d ₁	1 Length l ±0.1			2 Length l ±0.2			d ₂ Through hole for screw	d ₃ Thread	d ₄	d ₅	t min.
	Type A1	Type A2	Type A3								
22 0.87	10 0.394	12 0.472	16 0.630	20 0.79	30 1.181	50 1.969	M 5	M 6	18 0.71	22.8 0.90	12 0.47
28 1.10	12 0.472	16 0.630	20 0.787	30 1.18	50 1.969	75 2.953	M 6	M 8	24 0.94	28.8 1.13	16 0.63
34 1.34	12 0.472	16 0.630	20 0.787	30 1.18	50 1.969	100 3.937	M 8	M 10	30 1.18	34.8 1.37	20 0.79

Specification

- Body
Stainless steel AISI 316L
Matte finish (Ra < 0.8 µm) **MT**
- Sealing ring
- H-NBR **H**
Temperature resistant
-13 °F to +302 °F (-25 °C to +150 °C)
- EPDM **E**
Temperature resistant
-40 °F to +248 °F (-40 °C to +120 °C)
- Blue
- Hardness 85 ±5 shore A
- FDA compliant
- Plastic Characteristics → page QVX
- Stainless Steel Characteristics → page QVX
- RoHS compliant

Accessory

- Sealing rings GN 7600 → page QVX

On request

- with FKM sealing ring (Fluorine rubber) **F**

Information

Spacers GN 6226 are certified according to EHEDG and DGUV Test guidelines and are intended for use in hygiene areas. The sealed mounting surfaces enable fastening without dead spaces. The high quality finish prevents adherence of dirt and facilitates cleaning.

Spacers are used to fasten parts at an offset parallel to their plane of installation. This avoids doubling up on surfaces and leaves space for cleaning. The internal thread can alternatively be used as a through hole by a screw with a smaller thread.

see also...

- Product Family Hygienic Design → page QVX
- Hex Head Screws GN 1580 (Stainless Steel, Hygienic Design) → page QVX
- Nuts GN 1580 (Stainless Steel, Hygienic Design) → page QVX
- Hex Head Screws GN 1581 (Stainless Steel, Low-Profile Head, Hygienic Design) → page QVX
- Hexagon Head Screws GN 1582 (Stainless Steel, with Recessed Stud for Loss Protection, Hygienic Design) → page QVX

How to order	
1	Outer diameter d ₁
2	Length l
3	Type
4	Finish
5	Sealing ring material

GN 6226-28-75-A3-MT-H

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10