




- 2 Bore code**
- B** Without keyway
 - K** With keyway
 - V** With square

Specification

- Lever body**
Plastic, Polyamide (PA)
• Glass fiber reinforced
• Operating temperature
-22 °F to +266 °F (-30 °C to +130 °C)
• Black-gray, similar to RAL 7021, matte finish

- EN 623**
Hub
Steel, blackened finish
- EN 623.5**
Hub
Stainless steel AISI 303

- Cover cap**
Plastic, Polyamide (PA)
• Black-gray, RAL 7021, matte finish
• Orange, RAL 2004, matte finish
• Gray, RAL 7035, matte finish
• Yellow, RAL 1021, matte finish
• Blue, RAL 5024, matte finish
• Red, RAL 3000, matte finish
• Green, RAL 6017, matte finish
• Gray, RAL 7035, matte finish with arrow

- **DSG**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**
- **DGN**
- **PGR**

RoHS

On request

- Special inch and metric bores, threads or keyways

Operations are performed smoothly and powerfully thanks to the heavy-duty arm of the control levers EN 623 / EN 623.5. The enlarged and sunken semi-spherical end of this control lever offers a comfortable support for the palm of the hand and an effective grip. Cover caps are supplied but not assembled (press-fit, removable with screwdriver).

see also...	Page
GN 210 Control Levers (Zinc Die-Cast)	QVX
EN 512 Control Levers (Plastic, with Steel Hub)	QVX
GN 750 Control Levers (Steel, Blackened Finish)	QVX

Technical Information

Assembly Examples	QVX
Product Family Ergostyle®	QVX
Keyways WN 6885 / DIN 6885-1	QVX
Square Bores WN 79	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 184 Countersunk Washers (for Axial Fixing)	QVX
--	-----

How to order (Steel hub)

1	Diameter d ₁
2	Bore code
3	Bore d ₂ (Keyway, Square)
4	Color of the cover cap

EN 623-37-B 8-DGB

How to order (Stainless steel hub)

1	Diameter d ₁
2	Bore code
3	Bore d ₂ (Keyway, Square)
4	Color of the cover cap

EN 623.5-32-B 6-DSG

Metric table


1 3

Dimensions in: millimeters / inches


d ₁	d ₂ Bore H7 Square H11	b	d ₃	d ₄	d ₅	d ₆	d ₇	h ₁	h ₂	h ₃	h ₄	h ₅	h ₆	k	Length l	r	s	t
32 1.26	6* 0.236	20 0.79	15 0.59	22.5 0.89	16 0.63	10 0.39	4 0.16	24 0.94	35 1.38	24 0.94	18 0.71	2 0.08	3 0.12	24 0.94	67 2.64	12 0.47	4.3 0.17	9 0.35
37 1.46	8* 0.315	23 0.91	18 0.71	26 1.02	20 0.79	13.5 0.53	5 0.20	27 1.06	42 1.65	28 1.10	20 0.79	2.5 0.10	5 0.20	26 1.02	85 3.35	13.8 0.54	4.3 0.17	12.5 0.49
46 1.81	12 0.472	29 1.14	22 0.87	31.5 1.24	25.5 1.00	17 0.67	6 0.24	35 1.38	54 2.13	36 1.42	24 0.94	2 0.08	8 0.31	32 1.26	110 4.33	17.5 0.69	6.5 0.26	15.5 0.61
54 2.13	14 0.551	34 1.34	26 1.02	36 1.42	31 1.22	21 0.83	8 0.31	38 1.50	60 2.36	38 1.50	29.5 1.16	2.5 0.10	6 0.24	39 1.54	140 5.51	20.2 0.80	7.3 0.29	16 0.63

* Square only available for EN 623

Assembly Examples



Control lever EN 623 / EN 623.5 attached via a key / keyway, using countersunk washer GN 184 / GN 184.5 → Page XYZ.



Control lever EN 623 / EN 623.5 with ball and spring snap mechanism for indexing the position angle, attached with a cross pin.
The cross pin is to be attached at an angle of 45° to the shaft axis. These parts are not included and must be ordered separately.

More information on request.