




Metric table

Dimensions in: millimeters / inches						
d ₁	d ₂		h		Length l	
	MS	KLG	MS	KLG	MS	KLG
M 12 x 1.5	14 0.55	15 0.59	7.5 0.30	8 0.31	5 0.20	6 0.24
M 16 x 1.5	18 0.71	20 0.79	8 0.31	9 0.35	5 0.20	6 0.24
M 20 x 1.5	22 0.87	24 0.94	8.5 0.33	9.5 0.37	6 0.24	6 0.24
M 25 x 1.5	28 1.10	29.7 1.17	11 0.43	11.5 0.45	7 0.28	8 0.31
M 32 x 1.5	35 1.38	37.1 1.46	12 0.47	12 0.47	8 0.31	8 0.31
M 40 x 1.5	44 1.73	46 1.81	13 0.51	13 0.51	8 0.31	8 0.31
M 50 x 1.5	54 2.13	56.3 2.22	15 0.59	15 0.59	9 0.35	10 0.39
M 63 x 1.5	67 2.64	69.3 2.73	16 0.63	17 0.67	10 0.39	12 0.47

Specification

Threaded plug

- Brass
 - Nickel-plated
 - Operating temperature
-4 °F to +176 °F (-20 °C to +80 °C)
- Plastic, polyamide (PA)
 - Glass fiber reinforced
 - Operating temperature
-40 °F to +212 °F (-40 °C to +100 °C)
 - Gray, RAL 7035

O-ring for MS

Acrylonitrile butadiene rubber (NBR)

Protection class

- IP 68 for MS
- IP 54 for KLG

RoHS

Accessory

GN 62444.1 Thin Hex Nuts

MS

KLG

Page

QVX

Threaded plugs GN 62444.2 seal unused mounting holes for cord grips. They can be screwed into an existing internal thread or mounted in a through hole using a mounting nut. The metal versions include an O-ring for sealing against the enclosure. The plastic version is sealed without an additional sealing ring.

see also...	Page
GN 62444.2 Threaded Plugs (PG Thread)	QVX
GN 62444 Cord Grips (Metric Thread)	QVX
GN 62444.3 Multiple Sealing Inserts	QVX
GN 62444.4 Reducers (Metric Thread)	QVX

Technical Information

IP Protection Classes	QVX
Plastic Characteristics	QVX

How to order		1	Thread d ₁
GN 62444.2-M50x1.5-MS		2	Material