




Metric table

1

d ₁		d ₂		h		Length l	
MS	KLK	MS	KLK	MS	KLK	MS	KLK
PG 7	PG 7	15 0.59	15 0.59	7.5 0.30	8 0.31	5 0.20	6 0.24
PG 9	PG 9	18 0.71	19.1 0.75	8 0.31	9.5 0.37	5 0.20	6.5 0.26
PG 11	PG 11	22 0.87	22.1 0.87	8 0.31	10 0.39	5 0.20	6.5 0.26
PG 13.5	PG 13.5	24 0.94	25.2 0.99	9 0.35	10 0.39	6 0.24	6.5 0.26
PG 16	PG 16	26 1.02	27.1 1.07	9 0.35	10 0.39	6 0.24	6.5 0.26
PG 21	PG 21	32 1.26	33.2 1.31	10 0.39	12 0.47	6 0.24	8 0.31
PG 29	PG 29	40 1.57	44 1.73	12 0.47	12.5 0.49	8 0.31	8 0.31
PG 36	PG 36	50 1.97	55 2.17	15 0.59	14 0.55	9 0.35	10 0.39
-	PG 42	-	62 2.44	-	14 0.55	-	10 0.39
-	PG 48	-	68.3 2.69	-	16 0.63	-	12 0.47

Dimensions in: millimeters / inches

2

Specification

Threaded plug

• Brass

• Plastic, polyamide (PA)

• Nickel-plated

• Operating temperature

• Glass fiber reinforced

• Operating temperature

• Gray, RAL 7035

MS

KLK

O-ring for MS

Acrylonitrile butadiene rubber (NBR)

Protection class

• IP 68 for MS

• IP 54 for KLK

Threaded plugs GN 62444.2 seal unused mounting holes for cable glands. They can be screwed into an existing internal thread or mounted in a through hole using a mounting nut.

The metal versions include an O-ring for sealing against the enclosure. The plastic version is sealed without an additional sealing ring.

see also...

GN 62444 Cord Grips (PG Thread)

GN 62444.2 Threaded Plugs (Metric Thread)

GN 62444.3 Multiple Sealing Inserts

GN 62444.4 Reducers (Metric Thread)

Page

QVX

QVX

QVX

QVX

Technical Information

IP Protection Classes

Plastic Characteristics

QVX

QVX

Accessory

GN 62444.1 Thin Hex Nuts

QVX