



- 3 Type**
- N** Without plastic cap
 - G** With plastic cap, gliding
 - R** With rubber cap, non-skid

Metric table

1 d₁		2 h		3 d₂ +0.2		e ≈		s		Suitable for DIN 6332 grub screw
Type N / R	Type G									
50 1.97	50 1.97	11.5 0.45	9.2 0.36	3.7 0.15	2 0.08	M 12				
50 1.97	50 1.97	13.5 0.53	12.5 0.49	4 0.16	2 0.08	M 16				
60 2.36	60 2.36	13.5 0.53	12.5 0.49	4 0.16	2 0.08	M 16				
60 2.36	60 2.36	15.5 0.61	16.5 0.65	4.3 0.17	2 0.08	M 20				
80 3.15	-	18 0.71	12.5 0.492	8 0.31	2.5 0.10	M 16				
80 3.15	-	20 0.79	16.5 0.650	8.3 0.33	2.5 0.10	M 20				
100 3.94	-	20 0.79	12.5 0.492	11 0.43	3 0.12	M 16				
100 3.94	-	22 0.87	16.5 0.650	11.3 0.44	3 0.12	M 20				

Specification

- Body
Steel, zinc plated, blue passivated finish
- Retaining spring
Stainless steel AISI 301
- Cap
Plastic
- Type G
Technopolymer (Polyacetal POM)
White, RAL 9001
- Type R
Elastomer (TPE) ≈ 75 shore A
Black
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Accessory

- Grub screws DIN 6332 → page 1119
- Tommy screws DIN 6304 → page 547
- Tommy screws DIN 6306 → www.jwwinco.com

Information

GN 6311.3 thrust pads are used together with screws that have a thrust point (DIN 6332 grub screws, DIN 6304 / DIN 6306 tommy screws) to install and level devices and fixtures.

The innovative design of the retaining spring allows simple mounting and removal of the screw tip to the thrust pad.

The plastic cap (type G / R) prevents damage to delicate surfaces. Due to the large diameter d₁, the contact pressure remains within tolerable limits.

see also...

- Leveling Feet GN 6311.4 (Steel) → page 1476
- Leveling Feet GN 6311.6 (Stainless Steel) → page XYZ
- Thrust Pads DIN 6311 → page 1120
- Thrust Pads GN 6311.1 → page 1123

<p>How to order</p> <p>GN6311.3-60-15.5-N</p>	1	Outer diameter d ₁
	2	Height h
	3	Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10