



2 Type

B Mounting from the operator's side

Metric table

Dimensions in: millimeters - inches

1 l_1	2 d_1	d_2	h_1	h_2	l_2	l_3 min.	s	A/F	t
117 ±0.5 4.61 ±0.02	8.5 0.33	26 1.02	39 1.54	18 0.71	143 5.63	91 3.58	8.5 0.33	13	8.5 0.33
179 ±1 7.05 ±0.04	8.5 0.33	29 1.14	51 2.01	19 0.75	208 8.19	150 5.91	9.5 0.37	13	16 0.63

Specification

- Handle
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black-gray, RAL 7021, matte finish ● **SGA**
- White, RAL 9016, matte finish ○ **WSA**
- Cover caps
Plastic
Technopolymer (Polyamide PA)
- Black-gray for SGA
- White for WSA
- Strength Values → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

On request

- Various metric size fasteners and kit packaging

Information

EN 628.1 bridge handles are manufactured from an antimicrobial plastic.
Adding a silver-based substance has created a natural active agent which helps to prevent the growth of bacteria. Even after repeated cleaning with soap or solvent, the antimicrobial effect of this additive will not diminish. Sterilizing at temperatures below 266 °F (130 °C) will also have no effect on the antimicrobial property.
With these properties, operating parts made of this plastic are the perfect choice for use in medical engineering, in the food and the pharmaceutical industry, and in general wherever hygiene is of great importance.
see also...
• Product Family Sanline → page QVX
• Product Family Ergostyle® → page QVX
• Bridge Handles EN 628 (Mounting from the Back or from the Operator's Side) → page QVX

How to order	1 Length l_1
EN 628.1-117-8.5-B-SGA	2 Diameter d_1
	3 Type
	4 Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4