



Metric table

Dimensions in: millimeters - inches

¹ b ₁	² l ₁		Metric bolt size	Inch bolt size	b ₂	d	h	l ₂	l ₃
9 .35	100 3.94	-	M 8	5/16	30 1.18	12 .47	15 .59	30 1.18	18 .71
11 .43	125 4.92	-	M 10	3/8	30 1.18	16 .63	20 .79	36 1.42	24 .94
14 .55	160 6.30	200 7.87	M 14	1/2	40 1.57	20 .79	25 .98	45 1.77	30 1.18
18 .71	200 7.87	250 9.84	M 18	5/8	50 1.97	24 .94	30 1.18	55 2.17	36 1.42
22 .87	250 9.84	315 12.40	M 22	3/4	60 2.36	30 1.18	40 1.57	65 2.56	45 1.77
26 1.02	250 9.84	315 12.40	M 24	1	70 2.76	38 1.50	40 1.57	80 3.15	56 2.20
33 1.30	315 12.40	400 15.75	M 30	1 1/4	80 3.15	45 1.77	50 1.97	85 3.35	56 2.20

Specification

- Forked clamp
- Tempered steel
- Lacquer painted finish
- RoHS compliant

Information

DIN 6315C fork clamps with pin end and open slot have a large offering of clamp size options. They range from 3.94" (100 mm) to 15.75" (400 mm) in length with the ability to clamp small to very large parts.

see also...

- Tapered Fork Clamps DIN 6315B → page QVX
- Forked Clamps NO. 6315 GN → page QVX

How to order ¹ ² DIN 6315C-9-100	1	Width b ₁
	2	Length l ₁