



**Metric table**

Dimensions in: millimeters - inches

d	l <sub>1</sub>	Metric bolt size	Inch bolt size	b <sub>1</sub>	b <sub>2</sub>	h	l <sub>2</sub>	l <sub>3</sub>
6.6 0.26	50 1.97	M 6	1/4	20 0.79	8 0.31	10 0.39	10 0.39	20 0.79
9 0.35	60 2.36	M 8	5/16	25 0.98	10 0.39	12 0.47	13 0.51	22 0.87
11 0.43	80 3.15	M 10	3/8	30 1.18	12 0.47	15 0.59	15 0.59	30 1.18
14 0.55	100 3.94	M 14	1/2	40 1.57	14 0.55	20 0.79	21 0.83	40 1.57
14 0.55	125 4.92	M 14	1/2	40 1.57	14 0.55	20 0.79	21 0.83	50 1.97
18 0.71	125 4.92	M 18	5/8	50 1.97	18 0.71	25 0.98	26 1.02	45 1.77
18 0.71	160 6.30	M 18	5/8	50 1.97	18 0.71	25 0.98	26 1.02	65 2.56
22 0.87	160 6.30	M 22	3/4	60 2.36	22 0.87	30 1.18	30 1.18	60 2.36
22 0.87	200 7.87	M 22	3/4	60 2.36	22 0.87	30 1.18	30 1.18	80 3.15
26 1.02	200 7.87	M 24	1	70 2.76	26 1.02	30 1.18	35 1.38	80 3.15
26 1.02	250 9.84	M 24	1	70 2.76	26 1.02	35 1.38	35 1.38	105 4.13
33 1.30	250 9.84	M 30	1 1/4	80 3.15	34 1.34	40 1.57	45 1.77	100 3.94
33 1.30	315 12.40	M 30	1 1/4	80 3.15	34 1.34	50 1.97	45 1.77	130 5.12
43 1.69	400 15.75	M 42	1 1/2	100 3.94	43 1.69	60 2.36	100 3.94	150 5.91

**Specification**

- Plain clamp  
Tempered steel  
Water-base painted and ink jet printed
- RoHS compliant

**Accessory**

- T-slot bolts DIN 787 → page 1229
- Fixture nuts DIN 6330 → page 1140
- Heavy duty flat washers DIN 6340 → page 1152
- T-slot nuts DIN 508 → page 1221
- Double-ended threaded studs DIN 6379 → page 1227

**Information**

DIN 6314 plain clamps have an extensive range of clamping options. Small parts up to very large parts can be clamped using this particular clamp.

see also...

- Adjustable Plain Clamps NO. 6314 V → page 740 / 741

<b>How to order</b> <b>DIN 6314-26-200</b>	1	Diameter d
	2	Length l <sub>1</sub>