



- 3 Type**
- B** Cylindrical
 - C** Flattened

Metric table

Dimensions in: millimeters - inches

1 d ₁ g6	2 d ₂ n6	d ₃ ^{-0.01} / _{-0.05}	d ₄ Thread	h ₁	h ₂	Length l	s Type C	t	r
10 0.39	7 0.28	10 0.39	M 3	10 0.39	2.5 0.10	7 0.28	2.5 0.10	6 0.24	2.5 0.10
12 0.47	8 0.31	12 0.47	M 4	12 0.47	3 0.12	8 0.31	2.5 0.10	8 0.31	3 0.12
16 0.63	12 0.47	16 0.63	M 5	16 0.63	4 0.16	12 0.47	4.3 0.17	10 0.39	4 0.16
20 0.79	14 0.55	20 0.79	M 5	20 0.79	5 0.20	14 0.55	5 0.20	10 0.39	5 0.20
22 0.87	16 0.63	22 0.87	M 5	22 0.87	5.5 0.22	16 0.63	5 0.20	10 0.39	5.5 0.22
25 0.98	18 0.71	25 0.98	M 5	25 0.98	6 0.24	18 0.71	5.6 0.22	10 0.39	6 0.24

Specification

- Steel, hardened
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

Information

GN 6322 locating pins are inserted into bores for positioning, with the ball-type shoulder facilitating the insertion into the bore.

The flattened design of type C provides tolerance for the spacing of the two bores. Another application of this design is to affix parts to be positioned in one direction only.

see also...

- Press-Fit Drill Bushings DIN 172 / DIN 179 → page 1172

How to order	1 Diameter d ₁
	2 Diameter d ₂
	3 Type

GN 6322-16-12-B