



### Metric table

Dimensions in: millimeters - inches

<sup>1</sup> h	<sup>2</sup> d <sub>1</sub>	d <sub>2</sub>	e min.	Length l	s
10 0.39	M 6	8 0.31	11.5 0.45	11 0.43	10 0.39
15 0.59	M 8	10 0.39	15 0.59	13 0.51	13 0.51
20 0.79	M 6	6 0.24	11.5 0.45	11 0.43	10 0.39
20 0.79	M 10	13 0.51	19.6 0.77	16 0.63	17 0.67
25 0.98	M 12	15 0.59	21.9 0.86	20 0.79	19 0.75
30 1.18	M 8	9 0.35	15 0.59	13 0.51	13 0.51
40 1.57	M 10	13 0.51	19.6 0.77	16 0.63	17 0.67
50 1.97	M 12	15 0.59	21.9 0.86	20 0.79	19 0.75

### Specification

- Steel  
European Standard No. 1.0718  
- Unhardened  
- Blackened finish
- RoHS compliant

### Information

DIN 6320 jig feet are normally used in jig construction if neither a self-aligning support nor an axial adjustment is required.

How to order <sup>1</sup> <sup>2</sup> <b>DIN 6320-20-M6</b>	1 Height h
	2 Thread d <sub>1</sub>