



Inch | Metric

SS Stainless Steel

4 Type

K With tapped insert

Specification



<ul style="list-style-type: none"> Hand knob Plastic Duroplast (Phenolic PF) Black, shiny finish 	KU
<ul style="list-style-type: none"> Tapped insert - Steel, zinc plated, blue passivated finish - Brass - Stainless steel AISI 304 	— MS NI
<ul style="list-style-type: none"> Hand knob Plastic Technopolymer (Polyamide PA) - Shock-resistant - Black, matte finish 	KT
<ul style="list-style-type: none"> Tapped insert Steel, zinc plated, blue passivated finish 	—
<ul style="list-style-type: none"> Plastic Characteristics → page 2135 RoHS compliant 	

Information

Hand knobs DIN 6335 with plain bore H7 are available under the GN 6335.1 / GN 6335.2 series.

see also...

- Hand Knobs DIN 6335 (Cast Iron / Stainless Steel / Aluminum) → page 626
- Hand Knobs GN 6335.1 (Phenolic Plastic, with Protruding Hub) → page 628
- Hand Knobs GN 6335.2 (Technopolymer Plastic, with Protruding Hub) → page 628
- Hand Knobs DIN 6335 with Loss Protection GN 111.7 → page 628

<p>How to order (Inch, Technopolymer, steel insert)</p> <p style="text-align: center;">1 2 3 4</p> <p>DIN 6335-KT-40-5/16X18-K</p>	<p>1 Material</p> <p>2 Handle diameter d₁</p> <p>3 Thread d₂</p> <p>4 Type</p>
<p>How to order (Metric, Duroplast, stainless steel insert)</p> <p style="text-align: center;">1 2 3 4 5</p> <p>DIN 6335-KU-50-M10-K-NI</p>	<p>1 Material</p> <p>2 Handle diameter d₁</p> <p>3 Thread d₂</p> <p>4 Type</p> <p>5 Insert material</p>

Inch table

Dimensions in: inches - *millimeters*

d ₁	d ₂		d ₃	h ₁	h ₂	t min.
	Plastic KU Steel insert	Plastic KT Steel insert				
1.26 32	-	1/4 x 20	0.55 14	0.79 20	0.39 10	0.47 12
1.57 40	1/4 x 20	5/16 x 18	0.71 18	0.98 25	0.51 13	0.55 14
1.97 50	-	3/8 x 16	0.87 22	1.26 32	0.79 20	0.71 18
2.48 63	-	1/2 x 13	1.02 26	1.57 40	0.98 25	0.87 22

Metric table

Dimensions in: millimeters - *inches*

d ₁	d ₂				d ₃	h ₁	h ₂	t min.	
	Plastic KU Steel insert	Plastic KU Brass insert MS	Plastic KU Stainless steel insert NI	Plastic KT Steel insert				Steel insert Brass insert	Stainless steel insert
20 0.79	-	M 4	-	-	10 0.39	13 0.51	6 0.24	7 0.28	-
25 0.98	M 5	M 5	M 5	-	13 0.51	17 0.67	8 0.31	9.5 0.37	7.5 0.30
32 1.26	M 6	M 6	M 6	M 6	14 0.55	20 0.79	10 0.39	12 0.47	9 0.35
40 1.57	M 8	M 8	M 8	M 8	18 0.71	25 0.98	13 0.51	14 0.55	12 0.47
50 1.97	M 10	M 10	M 10	M 10	22 0.87	32 1.26	20 0.79	18 0.71	15 0.59
63 2.48	M 12	M 12	M 12	M 12	26 1.02	40 1.57	25 0.98	22 0.87	18 0.71
80 3.15	M 16	M 16	M 16	M 16	35 1.38	50 1.97	30 1.18	30 1.18	24 0.94
100 3.94	M 20	-	-	-	34 1.34	65 2.56	38 1.50	30 1.18	-

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

