



Metric table



Dimensions in: millimeters - inches

d ₁	d ₂	s	For screws with thread size
6.4 0.25	17 0.67	3 0.12	M 6
8.4 0.33	23 0.91	4 0.16	M 8
10.5 0.41	28 1.10	4 0.16	M 10
13 0.51	35 1.38	5 0.20	M 12
15 0.59	40 1.57	5 0.20	M 14
17 0.67	45 1.77	6 0.24	M 16
19 0.75	45 1.77	6 0.24	M 18
21 0.83	50 1.97	6 0.24	M 20
23 0.91	50 1.97	8 0.31	M 22
25 0.98	60 2.36	8 0.31	M 24
28 1.10	68 2.68	10 0.39	M 27
31 1.22	68 2.68	10 0.39	M 30
38 1.50	80 3.15	12 0.47	M 36
44 1.73	100 3.94	15 0.59	M 42
50 1.97	110 4.33	17 0.67	M 48

Specification

- Heat-treated steel
 - Tempered
 - Hardness (350 + 80) HV 30
 - Phosphate-treated
 - Punched, not deburred
- RoHS compliant

Information

DIN 6340 heavy duty washers are mainly used for elongated holes.

see also...

- Heavy Duty Washers GN 6339 → page 1148

How to order

DIN6340-17

1 Inner diameter d₁