



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂	l ₁					l ₂		d ₃		d ₄	h ₁	h ₂
		10	15	20	25	-	MS tip	KU tip	MS tip	KU tip			
25 <i>0.98</i>	M 5	10 <i>0.39</i>	15 <i>0.59</i>	20 <i>0.79</i>	25 <i>0.98</i>	-	0.5 <i>0.02</i>	1 <i>0.04</i>	3 <i>0.12</i>	3 <i>0.12</i>	12 <i>0.47</i>	16 <i>0.63</i>	8 <i>0.31</i>
32 <i>1.26</i>	M 6	10 <i>0.39</i>	16 <i>0.63</i>	20 <i>0.79</i>	25 <i>0.98</i>	30 <i>1.18</i>	1 <i>0.04</i>	1.3 <i>0.05</i>	4 <i>0.16</i>	3.5 <i>0.14</i>	14 <i>0.55</i>	20 <i>0.79</i>	10 <i>0.39</i>
40 <i>1.57</i>	M 8	20 <i>0.79</i>	25 <i>0.98</i>	30 <i>1.18</i>	40 <i>1.57</i>	50 <i>1.97</i>	1.5 <i>0.06</i>	1.6 <i>0.06</i>	6 <i>0.24</i>	5 <i>0.20</i>	18 <i>0.71</i>	25 <i>0.98</i>	13 <i>0.51</i>
50 <i>1.97</i>	M 10	20 <i>0.79</i>	25 <i>0.98</i>	30 <i>1.18</i>	45 <i>1.77</i>	55 <i>2.17</i>	2 <i>0.08</i>	1.9 <i>0.07</i>	8 <i>0.31</i>	6.5 <i>0.26</i>	22 <i>0.87</i>	32 <i>1.26</i>	17 <i>0.67</i>

Specification

- Star knob DIN 6336
Plastic
Technopolymer (Polyamide PA)
Black, matte finish
- Threaded stud
Stainless steel AISI 304 Cu
- Tip
 - Brass **MS**
 - Plastic (Polyacetal POM) **KU**
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

GN 6336.10 star knobs with stainless steel threaded stud are an excellent choice for corrosion-free applications.

The brass or plastic tip on the stud prevents indentations or other damage from occurring.

see also...

- Hollow Knurled Knobs GN 421.10 (with Brass / Plastic Tip) → www.jwwinco.com
- Wing Screws EN 633.10 (with Plastic Tip) → www.jwwinco.com
- Hollow Knurled Knobs GN 7336.5 (with Brass / Plastic Tip) → www.jwwinco.com
- Star Knobs GN 6336.10 with Loss Protection GN 111.7 → page 2046

How to order

GN 6336.10-32-M6-20-KU

- 1 Handle diameter d₁
- 2 Thread d₂
- 3 Length l₁
- 4 Tip material