



SS Stainless Steel

- 4 Type**
- K** With tapped insert
 - D** With tapped through bore (only available in metric sizes)

Specification

1 5

- Star knob
Plastic
Duroplast (Phenolic PF) **KU**
Black, shiny finish
- Tapped insert
 - Steel, zinc plated, blue passivated finish —
 - Brass **MS**
 - Stainless steel AISI 304 **NI**
- Star knob
Plastic
Technopolymer (Polyamide PA) **KT**
- Shock-resistant
- Black, matte finish
- Tapped insert
 - Steel, zinc plated, blue passivated finish —
 - Stainless steel AISI 303 **NI**
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- [RoHS compliant](#)

Information

DIN 6336 star knobs are an economical choice, yet offer top quality and ergonomic styling. The version with stainless steel insert is suitable for certain non-corrosive environment applications.

see also...

- *Star Knobs DIN 6336 (Cast Iron / Stainless Steel, Aluminum)* → page 572
- *Star Knobs GN 6336.1 (Phenolic, with Protruding Hub)* → page 574
- *Star Knobs GN 6336.2 (Technopolymer, with Protruding Hub)* → page 574
- *Star Knobs GN 6336.13 (with Loss Protection)* → page 584
- *Star Knobs DIN 6336 with Loss Protection GN 111.7* → page 2046

How to order (Inch, Duroplast, steel insert)	1 Material
DIN 6336-KU-50-1/4X20-K	2 Handle diameter d ₁
	3 Thread d ₂
	4 Type

How to order (Metric, Technopolymer, stainless steel insert)	1 Material
DIN 6336-KT-50-M10-K-NI	2 Handle diameter d ₁
	3 Thread d ₂
	4 Type
	5 Insert material

Inch table

Dimensions in: inches - *millimeters*

d ₁	d ₂		d ₃	h ₁	h ₂	t ₁ min.		t ₂
	Steel insert Plastic KU Type K	Plastic KT Type K						
0.98 25	-	10 x 32	0.47 12	0.63 16	0.31 8	0.37 9.5	-	
1.26 32	-	1/4 x 20	0.55 14	0.79 20	0.39 10	0.47 12	-	
1.57 40	-	5/16 x 18	0.71 18	0.98 25	0.51 13	0.55 14	0.51 13	
1.97 50	1/4 x 20	3/8 x 16	0.87 22	1.26 32	0.67 17	0.71 18	0.63 16	
2.48 63	5/16 x 18	1/2 x 13	1.02 26	1.57 40	0.83 21	0.87 22	0.79 20	
3.15 80	3/8 x 16	-	1.38 35	1.97 50	0.98 25	1.18 30	-	

Metric table

Dimensions in: millimeters - *inches*

d ₁	d ₂					d ₃	h ₁	h ₂	t ₁ min.			t ₂
	Steel insert Plastic KU Type K	Plastic KT Type K	Plastic KT Type D	MS insert Plastic KU Type K	NI insert Plastic KU / KT Type K				Steel insert MS insert NI insert (KT)	NI insert (KU)		
20 0.79	-	-	-	M 4	-	10 0.39	13 0.51	7 0.28	6.5 0.26	-	-	
25 0.98	-	M 4	-	-	-	12 0.47	16 0.63	8 0.31	7.5 0.30	-	-	
25 0.98	M 5	M 5	-	M 5	M 5	12 0.47	16 0.63	8 0.31	9.5 0.37	7.5 0.30	-	
25 0.98	-	M 6	-	-	-	12 0.47	16 0.63	8 0.31	9 0.35	-	-	
32 1.26	-	M 4	-	-	-	14 0.55	20 0.79	10 0.39	6.5 0.26	-	-	
32 1.26	-	M 5	-	-	M 5	14 0.55	20 0.79	10 0.39	9.5 0.37	7.5 0.30	-	
32 1.26	M 6	M 6	M 6	M 6	M 6	14 0.55	20 0.79	10 0.39	12 0.47	9 0.35	10.5 0.41	
40 1.57	M 6	M 6	-	M 6	M 6	18 0.71	25 0.98	13 0.51	12 0.47	9 0.35	-	
40 1.57	M 8	M 8	M 8	M 8	M 8	18 0.71	25 0.98	13 0.51	14 0.55	12 0.47	13 0.51	
40 1.57	-	M 10	-	-	-	18 0.71	25 0.98	13 0.51	14 0.55	-	-	
50 1.97	M 8	M 8	M 8	M 8	M 8	22 0.87	32 1.26	17 0.67	14 0.55	12 0.47	16 0.63	
50 1.97	M 10	M 10	M 10	M 10	M 10	22 0.87	32 1.26	17 0.67	18 0.71	15 0.59	16 0.63	
50 1.97	-	M 12	-	-	-	22 0.87	32 1.26	17 0.67	18 0.71	-	-	
63 2.48	M 10	M 10	-	M 10	M 10	26 1.02	40 1.57	21 0.83	18 0.71	15 0.59	-	
63 2.48	M 12	M 12	M 12	M 12	M 12	26 1.02	40 1.57	21 0.83	22 0.87	18 0.71	20 0.79	
63 2.48	-	M 16	-	-	-	26 1.02	40 1.57	21 0.83	22 0.87	-	-	
80 3.15	M 12	M 12	-	M 12	M 12	35 1.38	50 1.97	25 0.98	22 0.87	18 0.71	-	
80 3.15	M 16	M 16	-	M 16	M 16	35 1.38	50 1.97	25 0.98	30 1.18	24 0.94	-	

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

