




Identification no. 1

Identification no. 2

Metric

Type K



elesa

Original design GLA-1 / GLA-2


1 Type

- K** Ball-shaped rollers
- Z** Cylindrical rollers
- ZA** Cylindrically offset rollers



2 Identification no.

- 1** Single row
- 2** Double row

Type Z



Type ZA



Metric table

3

Dimensions in: millimeters / inches

| Length l | b ₁ | b ₂ | b ₃ | d ₁ | d ₂ | d ₃ | h ₁ | | h ₂ | h ₃ | Packaging unit |
|----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-----------|----------------|----------------|----------------|
| | | | | | | | Id. no. 1 | Id. no. 2 | | | |
| 1440 | 3000 | 25.5 | 25 | 26 | 12.5 | 11.3 | 47.5 | 93 | 81.5 | 36 | 2 |
| 56.69 | 118.11 | 1.00 | 0.98 | 1.02 | 0.49 | 0.44 | 1.87 | 3.66 | 3.21 | 1.42 | |


How to order

EN 6471-ZA-1-3000-AL-GR

- 1** Type
- 2** Identification no.
- 3** Length l
- 4** Material
- 5** Color

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10





Specification



Carrier profile

Aluminum **AL**
Anodized finish, natural color

Rollers

Plastic, polyethylene (PE)
• Operating temperature
-4 °F to 194°F (-20 °C to 90 °C)
• Gray



Axis

Stainless steel AISI 304

Axial mount

Plastic, polyacetal (POM)
• Operating temperature
-4 °F to 194°F (-20 °C to 90 °C)
• White

RoHS

Side guides EN 6471 are attached to the sides of conveyor sections and their rollers guide the conveyed goods without damage.

The type of rollers used depends on the conveyed material. Type K is used for cans and plastic boxes. For cardboard boxes, type Z can be used for an even material flow. For containers of glass, type ZA is used since it allows easy removal of any contamination due to glass breakage.

Side guides are fastened on the rear side via the T-slot. Connecting elements EN 6473.2 can be used for this purpose, for example.

The side guides are delivered in packaging units of 2 pieces each. They can be shortened in increments of 120 mm.

see also...

| | Page |
|--------------------------------------|-------------|
| EN 6472 Side Guides | QVX |
| EN 6476.2 Side Guide Brackets | QVX |

Technical Information

| | |
|---------------------------------|-----|
| Plastic Characteristics | QVX |
| Stainless Steel Characteristics | QVX |

Accessory

| | |
|--------------------------------------|-----|
| EN 6471.1 Lead-In Guides | QVX |
| EN 6471.2 End Caps | QVX |
| EN 6471.3 Connecting Strips | QVX |
| EN 6473.2 Connecting Elements | QVX |