

Metric




elesa
Original design MPG-T / MPG-C

SS Stainless Steel

1 Type

- T Retaining profile trapezoidal
- R Retaining profile round



Metric table

2			2					Dimensions in: millimeters / inches	
d			h	b ₀			l ₁	l ₂	
Type R			Type T	EN 6475	EN 6475.1	EN 6475.2			
B 10	B 12	B 14	17 0.67	18 / 21	18	20	26 1.02	15 0.59	

Specification

Clamp

- Plastic, Polyamide (PA)
- Operating temperature
-22 °F to 212 °F (-30 °C to +100 °C)
- Shock resistant
- Black

Socket cap screws / Nuts

Stainless steel AISI 304

RoHS

Technical Information

	Page
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Side guide clamps EN 6475.3 attach side guides to conveyor sections. This also requires the use of flat steel bars 25x8, connecting elements EN 6473.2 and side guide holders EN 6476, EN 6476.2 or EN 6476.3. Multiple side guides can be attached on top of each other.

The side guide is clamped using the socket cap screws. A screw on the application side is required for mounting on the flat bar

see also...

	Page
EN 6475 Side Guides (Guide Contour Flat)	QVX
EN 6475.1 Side Guides (Guide Contour Rounded)	QVX
EN 6475.2 Side Guides (Guide Contour Flat, Stepped)	QVX
EN 6473.2 Connecting Elements	QVX
EN 6476 Side Guide Bracket (Rigid, with Contact Edge)	QVX
EN 6476.2 Side Guide Bracket (Swiveling, with Contact Edge)	QVX
EN 6476.3 Side Guide Bracket (Swiveling)	QVX
GN 990 Construction Tubes	QVX

How to order

EN 6475.3-R-B10

- 1 Type
- 2 Diameter d (Height h)

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10