



Metric



Metric table

Dimensions in: millimeters / inches

1 d_1	2 d_2		3 $l_1 \pm 1$	b	h	l_2	l_3	l_4	t min.
30 1.18	M 6	M 8	400 15.75	22 0.87	90 3.54	440 17.32	360 14.17	480 18.90	15 0.59
30 1.18	M 6	M 8	500 19.69	22 0.87	94 3.70	540 21.26	460 18.11	580 22.83	15 0.59
30 1.18	M 6	M 8	600 23.62	22 0.87	98 3.86	640 25.20	560 22.05	680 26.77	15 0.59

Specification

Handle tube

Wall thickness 1.5 mm

• Aluminum

- Powder coated
Black, RAL 9005, textured finish ● **SW**
- Handle legs / Covers, black, matte finish
- Anodized finish, natural color ● **EL**
- Handle legs / Covers, black, matte finish
- Anodized finish, natural color ● **ES**
- Handle legs silver /
- Covers, light gray, matte finish

• Stainless steel AISI 304

- Ground, matte shiny finish ● **NG**
- Handle legs / Covers, black, matte finish

Handle legs

Aluminum

- Powder coated, textured finish
- Black, RAL 9005 (for SW / EL / NG)
- Silver, RAL 9006 (for ES)
- Threaded insert
- Steel, zinc plated

Covers

- Plastic, thermoplastic elastomer (TPE)
- Black, matte finish (for SW / EL / NG)
- Light gray, matte finish (for ES)

RoHS

On request

- Various metric size fasteners and kit packaging

Tubular arch handles GN 666.4 are an advanced development of GN 666 tubular handles with straight tube. The curved shape is another modern industrial design element.

see also...

GN 666 Tubular Grip Handles (Mounting from the Back) **Page** QVX

Technical Information

Load Capacity Information **QVX**

Plastic Characteristics **QVX**

Stainless Steel Characteristics **QVX**

How to order (Aluminum tube)

1 Handle diameter d_1
2 Thread d_2
3 Length l_1
4 Material / Finish

GN 666.4-30-M6-500-EL

How to order (Stainless steel tube)

1 Handle diameter d_1
2 Thread d_2
3 Length l_1
4 Material / Finish

GN 666.4-30-M8-400-NG

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4