



**SS** Stainless Steel

**4 Type**

- A** With cylindrical bore
- B** With bore for countersunk screw

**Metric table**

Dimensions in: millimeters - inches

<b>2</b> $d_1^{+0.5}_{+0.2}$	<b>3</b> $d_2$	$d_3$	$s$
4 0.16	10 0.39	13 0.51	8.4 0.33
5 0.20	13 0.51	16 0.63	10.5 0.41
6 0.24	15 0.59	20 0.79	12.6 0.50
8 0.31	20 0.79	26 1.02	16.8 0.66
10 0.39	25 0.98	32 1.26	21 0.83
12 0.47	30 1.18	40 1.57	25.2 0.99

**Specification**

- Steel, turned **ST**
- Blackened finish **BT**
- Zinc plated, blue passivated finish **ZB**
- Stainless steel AISI 303 **NI**
- Turned **MT**
- Matte shot-blasted finish
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

**Information**

GN 6341 washers are mainly used in mechanical machine and jig construction when DIN 125, DIN 9021 and DIN 6340 washers do not meet the requirements.

In particular, type B for countersunk screws is ideal for solid screw connections with a low construction height.

see also...

- *Heavy Duty Washers GN 6339* → page 1148
- *Countersunk Washers GN 184 / GN 184.5* → page 1150
- *Heavy Duty Flat Washers DIN 6340* → page 1152

<p>How to order</p> <p><b>GN6341-ST-8-26-B-ZB</b></p>	<b>1</b> Material
	<b>2</b> Inner diameter $d_1$
	<b>3</b> Outer diameter $d_2$
	<b>4</b> Type
	<b>5</b> Finish

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10