



**Metric table**

Dimensions in: millimeters - inches

Length l	d <sub>1</sub> H9 Bore	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	t	Ø Handle
38 1.50	B 6	15.5 0.61	11 0.43	3 0.12	21 0.83	12.5 0.49	41 1.61	7 0.28	15 0.59	12 0.47
56 2.20	B 8	19 0.75	13.5 0.53	4 0.16	28.5 1.12	18.5 0.73	51.5 2.03	8 0.31	20 0.79	13 0.51
71 2.80	B 10	23 0.91	16 0.63	4 0.16	30 1.18	18 0.71	53 2.09	9 0.35	25 0.98	14.5 0.57

**Specification**

- Crank body  
Plastic  
Technopolymer (Polyamide PA)  
- Special glass fiber reinforced  
- Temperature resistant up to 176 °F (80 °C)  
Black, RAL 9005, matte finish ● **SW**
- Hub bushing  
Brass
- Mini revolving handle  
Plastic  
Technopolymer  
- Black, matte finish  
- Threaded spindle  
Steel, zinc plated
- ISO Fundamental Tolerances → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

**Information**

Attaching the EN 670.2 crank handle on a shaft using a transverse pin or a set screw is made easier with the semilateral cross bore.

The finger recesses of the rotating cylinder head allows a safe grip and the ergonomic operation of the relatively small crank handle.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Product Family Ergostyle® → page QVX
- Commercial Crank Handles GN 369 (Steel, Nickel Plated) → page QVX

How to order <b>EN 670.2-38-B6-SW</b>	1	Length l
	2	Bore d <sub>1</sub>
	3	Color