



Inch | Metric



elesa
Original design EKK.



Inch table

¹ d ₁	² d ₂	d ₃	h ₁	h ₂	t _{min.}
0.83* 21	10 x 32	0.49 12.5	0.71 18	0.41 10.5	0.39 10
0.98* 25	1/4 x 20	0.57 14.5	0.89 22.5	0.55 14	0.47 12
1.22* 31	5/16 x 18	0.73 18.5	1.06 27	0.67 17	0.63 16

Dimensions in: inches / millimeters

*Only available in black, other colors on request

Metric table

¹ d ₁	² d ₂	d ₃	h ₁	h ₂	t _{min.}
16 0.63	M 3	-	8.5 0.33	8.5 0.33	6 0.24
18 0.71	M 4	-	10.5 0.41	10.5 0.41	6 0.24
21 0.83	M 4	M 5	12.5 0.49	10.5 0.41	10 0.39
25 0.98	M 6	M 8	14.5 0.57	14 0.55	12 0.47
31 1.22	M 6	M 8	18.5 0.73	17 0.67	15 0.59
31 1.22	M 10	-	18.5 0.73	17 0.67	17 0.67
35 1.38	M 6	M 8	20 0.79	17 0.67	15 0.59
35 1.38	M 10	-	20 0.79	17 0.67	17 0.67

Dimensions in: millimeters / inches

Specification

Knob

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -22 °F to +266 °F (-30 °C to +130 °C)
- Color
 - Black-gray, RAL 7021, matte finish
 - Red, RAL 3000, matte finish
 - Orange, RAL 2004, matte finish
 - Gray, RAL 7035, matte finish
 - Yellow, RAL 1021, matte finish
 - Blue, RAL 5024, matte finish
 - Green, RAL 6017, matte finish

- **SG**
- **RT**
- **OR**
- **GR**
- **GB**
- **BL**
- **GN**

Tapped insert

Brass

RoHS

When used as a push-pull button, the thumb rests naturally on the concave front surface, making it easier to grip the knurled knob EN 676. The slight knurling on the rim of the knob makes tightening or clamping operations easier.

Resistant to solvents, oils, grease and other chemical agents.

see also...

	Page
GN 676.1 Push / Pull Knobs (Steel, Blackened Finish)	QVX
GN 676.5 Push / Pull Knobs (Stainless Steel)	QVX
GN 76 Mushroom Shaped Knobs (Plastic)	QVX
EN 676 Knurled Knobs	QVX

Technical Information

Product Family Ergostyle®	QVX
Plastic Characteristics	QVX

How to order (Inch)

¹²³
EN 676-21-10X32-SG

- 1** Handle diameter d₁
- 2** Thread d₂
- 3** Color

How to order (Metric)

¹²³
EN 676-25-M6-RT

- 1** Handle diameter d₁
- 2** Thread d₂
- 3** Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

