

Metric




**elesa**  
Original design TTA. / TTB.

**SS** Stainless Steel

**2** Type

- D** With slotted holes
- E** With bores

**Application example**



**Metric table**



Dimensions in: millimeters / inches

d	Type E	Pipe size (inch) DIN EN 10220 / EN 10255
Bore Type D		
B 42.4	-	1 1/4"
B 48.3	B 48.3	1 1/2"
B 50.8	-	-
B 60.3	-	2"

**Specification**

**Support head**

- Plastic, polyamide (PA)
- Glass fiber reinforced
- Operating temperature  
-22 °F to 212 °F (-30 °C to +100 °C)
- Black, matte finish

**Clamping set**

- Stainless steel AISI 304
- Hex head screw DIN 931
- Hex nut DIN 934
- Washers DIN 125

RoHS

**On request**

Type D with square 45 x 45

Support heads EN 6470.2 are used in combination with boiler or threaded tubes to build transport systems or work tables. They connect the structure, e.g. with conveyor belts or control panels, at a right angle to the tube axis.

see also...

	Page
<b>EN 6470</b> Support Bases	QVX
<b>EN 6470.1</b> Cross Connectors	QVX
<b>EN 6470.3</b> Side Support Heads	QVX

**Technical Information**

	Page
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

**EN 6470.2-B48.3-E**

- 1** Bore d
- 2** Type

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

