



Top views for various bore Ø d<sub>1</sub>

Shaft collar  
GN 7062.1 / GN 7072.1



SS Stainless Steel

**3** Type

L Angled

**Metric table**

Dimensions in: millimeters - inches

m <sub>0</sub>	1 d <sub>1</sub> +0.1 Bore				2								m	s
	B 8	B 12	B 18	B 30	k	d <sub>2</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>	l <sub>6</sub>		
8 0.31	B 8	B 12	-	-	14 0.55	3.5 0.14	13 0.51	9.5 0.37	15 0.59	19 0.75	-	-	8 0.31	2 0.08
10 0.39	B 8	B 12	B 18	-	18 0.71	4.5 0.18	14.5 0.57	10.5 0.41	19 0.75	24.5 0.96	29.5 1.16	-	10 0.39	2 0.08
12 0.47	B 8	B 12	B 18	B 30	23 0.91	4.5 0.18	17 0.67	12.5 0.49	19 0.75	24.5 0.96	29.5 1.16	35.5 1.40	12 0.47	2.5 0.10
18 0.71	B 8	B 12	B 18	B 30	30 1.18	5.5 0.22	18.5 0.73	12.5 0.49	24.5 0.96	24.5 0.96	29.5 1.16	35.5 1.40	18 0.71	2.5 0.10

**Specification**

- Stainless steel AISI 304  
Matte shot-blasted finish
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

**Information**

GN 7062.10 sensor brackets are designed for holding sensors that are attached with two lock nuts. The bores d<sub>2</sub> match the tapped attachment holes of GN 7062.1 / GN 7072.1 shaft collars and facilitate an axial or radial positioning of the sensors.

see also...

- *Semi-Split Shaft Collars GN 7062.1 (Stainless Steel, with Tapped Attachment Holes)* → page 1207
- *Split Shaft Collars GN 7072.1 (Stainless Steel, with Tapped Attachment Holes)* → page 1215

How to order

**GN 7062.10-B18-30-L**

- 1 Bore d<sub>1</sub>
- 2 Width k
- 3 Type

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10