




Type K

Identification no. 1

Identification no. 2

Metric



elesa

Original design GLB-1 / GLB-2

SS Stainless Steel

1 Type

K Ball-shaped rollers

Z Cylindrical rollers



ZA Cylindrically offset rollers

2 Identification no.




1 Single row

2 Double row

Type Z



Type ZA



Metric table

3


Dimensions in: millimeters / inches

l ₁	b ₁	b ₂	b ₃	d ₁	d ₂	d ₃	h ₁		h ₂	h ₃	l ₂
							Id. no. 1	Id. no. 2			
375 14.76	31.2 1.23	30.6 1.20	31.8 1.25	12.5 0.49	11.3 0.44	13.5 0.53	44 1.73	79.8 3.14	71.8 2.83	35.5 1.40	75 2.95

How to order

- 1 Type
- 2 Identification no.
- 3 Length l₁
- 4 Material
- 5 Color

EN 6473-Z-2-375-POM-GR



Specification



Carrier profile segment

Plastic, polyacetal **POM**
 Black

Rollers

Plastic, polyethylene (PE)
 • Operating temperature
 -4 °F to 194 °F (-20 °C to 90 °C)
 • Gray **GR**

Axis

Stainless steel AISI 304

RoHS

Accessory

	Page
EN 6473.1 Retaining Profiles	QVX
EN 6473.2 Connecting Elements	QVX

Side guide segments EN 6473 are attached to the sides of conveyor sections, and their rollers guide the conveyed goods without damage. Due to their segmentation, they are particularly suited for use on curves.

The type of rollers used depends on the conveyed material. Type K is used for cans and plastic boxes. For cardboard boxes, type Z can be used for an even material flow. For containers of glass, type ZA is used since it allows easy removal of any contamination due to glass breakage.

Fastening is carried out with retaining profiles EN 6473.1, which are attached to conveyor systems with connecting elements EN 6473.2.

Included are 5 segments with total length l_1 .

see also...

	Page
EN 6471 Side Guides	QVX
EN 6472 Side Guides	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

