



Metric



Drive SL for slotted screwdriver



**elesa**  
Original design DT.653-AV

**9 Identification no.**

**3** With drive for slotted screwdriver

Metric table

Dimensions in: millimeters / inches

<b>d<sub>1</sub></b>	<b>Length l</b>					<b>d<sub>2</sub></b>	<b>k</b>	Drive SL for slotted screwdriver	Max. tightening torque in Nm
M 4	8 0.31	12 0.47	16 0.63	20 0.79	-	16 0.63	3.5 0.14	SL 6.5	0.5
M 5	8 0.31	12 0.47	16 0.63	20 0.79	25 0.98	20 0.79	4 0.16	SL 10	0.8
M 6	12 0.47	16 0.63	20 0.79	25 0.98	30 1.18	24 0.94	5 0.20	SL 12	1
M 8	15 0.59	20 0.79	25 0.98	30 1.18	-	30 1.18	6 0.24	SL 14	2.5

**Specification**

**Plastic**, polyamide (PA-HP)

- Glass fiber reinforced
- Operating temperature -22 °F to 212 °F (-30 °C to +100 °C)
- Black similar to RAL 9005, matte finish

● **SW**

RoHS

**On request**

- Gray similar to RAL 7040, matte finish ○ **GR**

Knurled thumb screws EN 653.9 are made of plastic, making them lightweight, resistant to corrosion and electrically insulating. They can be used for performing tool-free adjustments or clamping operations on fixtures and mechanisms.

As an alternative to the knurling, the slot on the face side allows a slotted screwdriver to be used.

For manufacturing reasons, the pivot has a hole on its face side.

see also...

	Page
<b>DIN 464</b> Knurled Thumb Screws (Steel, High Type)	QVX
<b>GN 464.2</b> Knurled Thumb Screws (with Thin Shank for Loss Prevention, High Type)	QVX
<b>DIN 653</b> Knurled Thumb Screws (Steel)	QVX
<b>GN 653.2</b> Knurled Thumb Screws (with Thin Shank for Loss Protection, Flat Type)	QVX
<b>GN 535</b> Knurled Screws (Stainless Steel)	QVX

**Technical Information**

Plastic Characteristics	QVX
-------------------------	-----

How to order

<b>1</b> Thread <b>d<sub>1</sub></b>
<b>2</b> Length <b>l</b>
<b>3</b> Identification no.
<b>4</b> Color

**EN 653.9 -M6-20-3-SW**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

