



SS Stainless Steel

3 Type

- A Flat spindle tip
- B Rounded spindle tip

Metric table

Dimensions in: millimeters - inches

1 d ₁ Thread	2 Length l			d ₂	d ₃	h	m	r
M 4	23 0.91	30 1.18	-	8 0.31	9.8 0.39	5 0.20	2.2 0.09	6 0.24
M 4	33 1.30	43 1.69	-	8 0.31	8 0.31	10 0.39	2.2 0.09	6 0.24
M 5	45 1.77	55 2.17	-	10 0.39	9 0.35	11 0.43	2.7 0.11	8 0.31
M 6	35 1.38	55 2.17	65 2.56	13 0.51	12 0.47	12 0.47	3.2 0.13	10 0.39
M 8	43 1.69	68 2.68	-	16 0.63	14 0.55	18 0.71	4 0.16	12 0.47
M 10	50 1.97	77 3.03	97 3.82	20 0.79	18 0.71	21 0.83	5 0.20	15 0.59
M 12	100 3.94	130 5.12	-	25 0.98	23 0.91	24 0.94	6 0.24	18 0.71

Specification

4

- Threaded spindle
 - Steel, zinc plated, blue passivated finish **ST**
 - Stainless steel AISI 304 **NI**
- Hex nuts ISO 4035
 - Steel, zinc plated, blue passivated finish
 - Stainless steel AISI 304
- Spindle tip
 - Rubber CR (Neoprene)
 - 85 shore A ≈
 - Vulcanized
 - Black
- [Elastomer Characteristics → page 2135](#)
- [Stainless Steel Characteristics → page 2143](#)
- [RoHS compliant](#)

Information

GN 708.1 spindle assemblies are primarily used with toggle clamps. They provide non-marking, yet secure clamping or holding of the workpiece via the toggle clamp.

The hex nuts are included.

see also...

- [Clamp Mounts GN 801 \(for Toggle Clamps with Forked Clamping Arm\) → www.jwwinco.com](#)
- [Clamp Mounts GN 809 \(for Toggle Clamps with Solid Clamping Arm\) → www.jwwinco.com](#)

How to order

GN 708.1-M5-45-A-NI

- 1** Thread d₁
- 2** Length l
- 3** Type
- 4** Material