



Metric table

Dimensions in: millimeters - inches

¹ d ₁ Pipe thread	¹ d ₂ Bayonet mount	² l ₁	d ₃	d ₄	d ₅	d ₆	l ₂	l ₃	l ₄	l ₅
G 1 1/4	-	94 3.70	83 3.27	56 2.20	-	49 1.93	23 0.91	9 0.35	-	-
-	BA 39	94 3.70	83 3.27	-	58 2.28	49 1.93	-	-	20 0.79	7 0.28

Specification

- Threaded flange
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Black, matte finish
- Filler strainer
Plastic
Technopolymer (Polypropylene PP)
- Glass fiber reinforced
- Black, matte finish
- Temperature resistant up to 194 °F (90 °C)
- Flange for bayonet mounting
Steel, zinc plated, blue passivated finish
- Seal
Cork, impregnated with rubber
- *Plastic Characteristics* → page 2135
- RoHS compliant

On request

- Mounting flange without filler strainer

Information

EN 664 filler strainers have a mounting flange for threaded or bayonet mount (BA) mounting of the breather cap. The strainer prevents the penetration of coarse impurities during the filling process.

Six self-tapping screws are included.

1) Breather caps are to be ordered separately.

see also...

- *Filler Strainers EN 664.1 (Side Installation)* → www.jwwinco.com
- *Breather Caps EN 663* → page 1694
- *Breather Valve Caps EN 774* → page 1696
- *Breather Check Valve Caps EN 774.1* → www.jwwinco.com

<p>How to order</p> <p>¹ ²</p> <p>EN 664-BA39-94</p>	1	Bayonet mount d ₂ (Pipe thread d ₁)
	2	Strainer length l ₁



Filler Strainers EN 664 with Breather Caps

Mounting dimensions (hole pattern)

