


Assembly instruction



Metric table

Dimensions in: millimeters - inches

¹ b ±0.2	² Length l in meters									s
10 0.394	0.5	1	1.5	2	2.5	3	4	5		1.66 0.07

Specification

- Magnetic band
 - Magnetic strip
 - Magnetized plastic band
 - Coefficient of expansion $17 \times 10^{-6}/K$
 - Pole length 5 mm, precision $\pm 40 \mu m$
 - Carrier strip
 - Stainless steel
 - Acrylate adhesive strip
- Cover strip
 - Protective strip
 - Stainless steel
 - Acrylate adhesive strip
- Temperature range:
 - 40 °F ... +212 °F (-40 °C ... +100 °C)
- RoHS compliant

Information

Magnetic bands EN 7110.2 are designed as accessories for magnetic measuring systems EN 7110 and are fastened using adhesive strips.

They consist of two separate parts, the magnetic band and the cover strip. The cover strip protects the magnetic band from damage.

The magnetic bands can be glued on all clean and suitable surfaces. The cover strip is then glued on the magnetic band.

see also...

- *Magnetic Measuring Systems EN 7110* → page QVX

On request

- Magnetic band in other lengths

How to order	¹ ² EN 7110.2-10-1	1 Width b
		2 Length l