



Inch




SS Stainless Steel

3 Type

- W** Figures horizontally arranged (Figure sequences L, M, R)
- S** Figures vertically arranged (Figure sequences U, M, O)

GN 711.1



Application example



Inch table

2

Dimensions in: inches / millimeters

| Length I (Scale) | 4.00 | 6.00 | 8.00 | 12.00 | 18.00 |
|------------------|-------|-------|-------|-------|-------|
| | 101.6 | 152.4 | 203.2 | 304.8 | 457.2 |

Specification

| | |
|------------------------|------------|
| Stainless steel | NI |
| • Thickness 0.02" | |
| • Scale etched | |
| Plastic | KUS |
| • Thickness 0.01" | |
| • Silver | |
| • Scale printed | |

RoHS

Rulers GN 711 are a convenient measuring device for such applications where consistency, repeatability and accuracy measuring various lengths and heights in either a vertical or horizontal position is important.

The position of linear actuator connectors can be easily read from rulers GN 711. With reference arrows GN 711.1, reference points can be marked on rulers or reference positions in machines.

To apply the ruler, remove the protective strip on the back and affix to a clean and dry surface. The engraved side of the stainless steel version is also protected by a strip of plastic film.

Indicator arrows GN 711.1 for rulers are to be ordered separately.

| see also... | Page |
|--|------|
| GN 711.2 Rulers (Aluminum, with Mounting Holes) | QVX |
| GN 711.3 Indicator Arrows (Aluminum, with Mounting Holes) | QVX |

| How to order (Ruler) | |
|---------------------------|--|
| 1 Material | |
| 2 Length I (Scale) | |
| 3 Type | |
| 4 Figure sequences | |

GN 711-KUS-2.00-S-M

| How to order (Indicator arrow) | |
|--------------------------------|--|
| 1 Material | |

GN 711.1-KUS

