



SS Stainless Steel

4 Type

A Both ends rounded

Metric table

Dimensions in: millimeters - inches

b h9	h	Length l														For shaft Ø from ... to
3 0.12	3 0.12	6 0.24	8 0.31	10 0.39	12 0.47	14 0.55	16 0.63	18 0.71	20 0.79	-	-	-	-	-	-	8...10
4 0.16	4 0.16	10 0.39	12 0.47	14 0.55	16 0.63	18 0.71	20 0.79	22 0.87	25 0.98	28 1.10	32 1.26	-	-	-	-	10...12
5 0.20	5 0.20	10 0.39	12 0.47	14 0.55	16 0.63	18 0.71	20 0.79	22 0.87	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	12...17
6 0.24	6 0.24	14 0.55	16 0.63	18 0.71	20 0.79	22 0.87	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	56 2.20	63 2.48	17...22
8 0.31	7 0.28	16 0.63	18 0.71	20 0.79	22 0.87	24 0.94	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	56 2.20	63 2.48	22...30
10 0.39	8 0.31	20 0.79	22 0.87	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	56 2.20	63 2.48	70 2.76	80 3.15	90 3.54	30...38
12 0.47	8 0.31	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	56 2.20	63 2.48	70 2.76	80 3.15	90 3.54	100 3.94	-	38...44

Specification



- Stainless steel AISI 316Ti **NI**
- ISO Fundamental Tolerances → page QVX
- Stainless Steel Characteristics → page QVX
- RoHS compliant

On request

- b = 14, 16, 18, 20 mm

Information

- see also...
- Keyway Type in the Bore or Shaft → page QVX

How to order

DIN 6885-10-8-36-A-NI

1	Width b
2	Height h
3	Length l
4	Type
5	Material