



- 4 Type**
- C** With threaded stud, without safety catch
 - CS** With threaded stud, with safety catch
 - B** With plain stud, without safety catch
 - BS** With plain stud, with safety catch

Metric table

Dimensions in: millimeters - inches

1 d_1 H9/h9	2 d_2 Right hand thread Left hand thread	3 l_2	d_3 Thread	d_4 h11	d_5	d_6	l_1	l_3	l_4	t min.	A/F	Min. pull-off force
8 0.31	M 5 M 5L	4 0.16 0.30	M 5	5 0.20	8 0.31	12.8 0.50	10 0.39	8.5 0.33	22 0.87	10.5 0.41	7	30 N 6.74 lbf
10 0.39	M 6 M 6L	4.5 0.18 0.31	M 6	6 0.24	10 0.39	14.8 0.58	12.5 0.49	10.5 0.41	25 0.98	11.5 0.45	8	40 N 8.99 lbf
13 0.51	M 8 M 8L	5 0.20 0.39	M 8	8 0.31	13 0.51	19.3 0.76	16.5 0.65	12 0.47	30 1.18	14 0.55	11	60 N 13.49 lbf
16 0.63	M 10 M 10L	6 0.24 0.51	M 10	10 0.39	16 0.63	24 0.94	20 0.79	15 0.59	35 1.38	15.5 0.61	13	80 N 17.98 lbf
16 0.63	M 12 M 12L	6 0.24 0.51	M 12	10 0.39	16 0.63	24 0.94	20 0.79	15 0.59	35 1.38	15.5 0.61	13	80 N 17.98 lbf
19 0.75	M 14F (≅ M 14 x 1.5)	M 14FL (≅ M 14 x 1.5L)	M 14 x 1.5	14 0.55	22 0.87	30 1.18	28 1.10	19.5 0.77	45 1.77	21.5 0.85	16	100 N 22.48 lbf

Specification

- Housing and threaded stud
Steel
 - Property class 5
 - Zinc plated, colorless passivated finish
- Ball
Steel
 - Hardened
 - Ball socket lubricated
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

Accessory

- Dust Caps GN 710 → page 1753

On request

- Reduced resistance (ball socket with play)
- Ball studs DIN 71803
- Ball sockets DIN 71805
- Ball joints
(ball socket and ball stud in one axis)

Information

DIN 71802 threaded ball joint linkages consist of a DIN 71805 ball socket and a DIN 71803 ball stud. The swivel angle for the type with safety catch (types CS, BS) is 15°, without safety catch (types C, B) it is 18°.

During assembly, the ball socket is pushed over the snap ring, which acts as a retainer. If the retaining force (see also pull-off force in the table above) is not sufficient, the connection of ball socket / ball stud can be secured by the safety catch, which can easily be fitted.

To protect the threaded ball joint linkages against contamination, GN 710 dust caps can be used. The hex nut is part of the threaded ball joint linkages with threaded stud.

see also...

- Angled Ball Joints DIN 71802 (Stainless Steel) → page 1752
- Axial Ball Joints GN 782 → page 1754

How to order (With threaded stud)	1 Diameter d_1
DIN 71802-19-M14FL-CS	2 Thread d_2
	4 Type

How to order (With plain stud)	1 Diameter d_1
DIN 71802-13-M8-10-B	2 Thread d_2
	3 Length l_2
	4 Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10