


Metric



SS Stainless Steel

4 Type

A Both ends rounded

Metric table

1 **2** **3**

Dimensions in: millimeters / inches

b h9	h	Length l														For shaft Ø from ... to
3 0.118	3 0.12	6 0.24	8 0.31	10 0.39	12 0.47	14 0.55	16 0.63	18 0.71	20 0.79	-	-	-	-	-	-	8...10
4 0.157	4 0.16	10 0.39	12 0.47	14 0.55	16 0.63	18 0.71	20 0.79	22 0.87	25 0.98	28 1.10	32 1.26	-	-	-	-	10...12
5 0.197	5 0.20	10 0.39	12 0.47	14 0.55	16 0.63	18 0.71	20 0.79	22 0.87	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	12...17
6 0.236	6 0.24	14 0.55	16 0.63	18 0.71	20 0.79	22 0.87	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	56 2.20	63 2.48	17...22
8 0.315	7 0.28	16 0.63	18 0.71	20 0.79	22 0.87	24 0.94	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	56 2.20	63 2.48	22...30
10 0.394	8 0.31	20 0.79	22 0.87	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	56 2.20	63 2.48	70 2.76	80 3.15	90 3.54	30...38
12 0.472	8 0.31	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	56 2.20	63 2.48	70 2.76	80 3.15	90 3.54	100 3.94	-	38...44

Specification

Stainless steel AISI 316Ti

5

NI

RoHS

On request

b = 14, 16, 18, 20 mm

see also...

DIN 6885 Parallel Keys (Steel)

Page

QVX

Technical Information

Keyways WN 6885 / DIN 6885-1 (High Type)

QVX

Keyways DIN 6885-2 (Low Type)

QVX

ISO Fundamental Tolerances

QVX

Stainless Steel Characteristics

QVX

How to order

1	Width b
2	Height h
3	Length l
4	Type
5	Material

DIN 6885-10-8-36-A-NI

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

