



Metric table

Dimensions in: millimeters - inches

Dimensions of shaft collars			Dimensions of damping washers				
d ₁	d ₂ Bore series		d ₃	d ₄ Bore series		b ±0.2	s
	1	2		1	2		
30 1.18	B 12	-	28 1.10	13 0.51	-	2 0.08	2.1 0.08
32 1.26	B 14	-	30 1.18	15 0.59	-	2 0.08	2.1 0.08
36 1.42	B 15	B 16	34 1.34	16 0.63	17 0.67	2 0.08	2.1 0.08
42 1.65	B 18	B 20	39 1.54	19.5 0.77	21.5 0.85	3 0.12	3 0.12
48 1.89	B 22	B 25	45 1.77	23.5 0.93	26.5 1.04	3 0.12	3 0.12
55 2.17	B 28	B 30	52 2.05	29.5 1.16	31.5 1.24	3 0.12	3 0.12
60 2.36	B 32	B 35	57 2.24	33.5 1.32	36.5 1.44	3 0.12	4 0.16
65 2.56	B 40	-	62 2.44	41.5 1.63	-	3 0.12	4 0.16

Specification

- Washer
Elastomer (PUR)
- 70 shore A
- Temperature resistant up to 176 °F (80 °C)
- Transparent
- Adhesive film
- Acrylate dispersion, solvent-free
- Strong adhesion
- *Plastic Characteristics* → page 2135
- RoHS compliant

Information

GN 7062.30 and GN 7072.30 damping washers are designed as accessories for semi-split shaft collars / split shaft collars and are attached with the help of an adhesive film, preferably on the groove-less side of the shaft collar. They absorb mild shocks and have a sound-damping effect when the shaft collars come into contact with other components.

In general, after removing the protective film, the damping washers can be attached to any suitable and clean surface.

GN 7062.3 semi-split shaft collars (→ page 1209) and GN 7072.3 split shaft collars (→ page 1217) are generally offered with assembled damping washers.

How to order (For semi-split shaft collars)	1	Outer diameter d ₁
	2	Bore d ₂
GN 7062.30-42-B18		
How to order (For split shaft collars)	1	Outer diameter d ₁
	2	Bore d ₂
GN 7072.30-60-B35		