



**3 Type**

**A** Mounting with countersunk screw

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> r	<b>2</b> d <sub>1</sub> Thread	b	d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	Max. load <b>F</b>
45 1.77	M 6	13 0.51	19 0.75	9 0.35	12 0.47	13 0.51	8.5 0.33	0.5 0.02	500 N 112 lbf
65 2.56	M 8	18 0.71	25 0.98	14 0.55	14 0.55	16 0.63	10.5 0.41	0.6 0.02	1000 N 225 lbf

**Specification**

- Lever arm  
Zinc die-cast  
Powder coated  
Black, RAL 9005, textured finish  
Silver, RAL 9006, textured finish
- Indexing mechanism  
Stainless steel
- Countersunk screw DIN 7991  
Stainless steel A2
- RoHS compliant



**Information**

GN 720 stop latches may be used as stops, and feature a high degree of stability. The internal ball spring indexing mechanism has four latching positions at a distance of 90° each. Thanks to the bolt attachment using the countersunk screw, the latching position can be easily selected. The latch arm is solid and may be machined, if required. The countersunk screw is enclosed as part of the assembly.

<b>How to order</b>	<b>1</b> Radius r
	<b>2</b> Thread d <sub>1</sub>
	<b>3</b> Type
	<b>4</b> Color

**GN 720-65-M8-A-SW**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

